



Specifications

Nominal Diameter	: 15 Inches
Rated Impedance	: 4Ω
Operating Bandwidth	: 30Hz to 2kHz (-3dB)
Power Handling Capacity	: 200W
RMS Power	: 100W
Sensitivity (1W/M)	: 93dB (±3dB)
Voice Coil Diameter	: 3 inch


Thiele-Small Parameters


Resonance Frequency	: Fs: 32.3Hz
DC Resistance	: Re: 3.4Ω
Mechanical Q Factor	: Qms: 3.0711
Electrical Q Factor	: Qes: 0.5251
Total Q Factor	: Qts: 0.4485
Equivalent Cas Air Load	: Vas: 223.2L
Surface Area of Cone	: Sd: 0.086m ²
Efficiency Bandwidth Product	: EBP: 61
Voice Coil Over Hang	: X-mas: 7mm

Physical Information

Basket	: Pressed steel chassis
Magnet Type	: 67 oz.
Cone Material	: Paper
Surround	: Cloth
Dust Cap	: PP
Damper	: Cloth

Rating Curves





Part Number Table

Description	Part Number
Woofer with Paper Cone and Cloth Surround, 4Ω, 15"	55-3213

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.