

## TECHNICAL DATA

# Fluke 28 II Ex Intrinsically Safe True RMS Digital Multimeter



## Key features

- A completely sealed, IP67 rated case
- Withstands drops up to 10 ft or 3 m (with holster)
- Dustproof per IEC 60529 IP6x
- Waterproof per IEC 60529 IPx7
- CAT III 1000 V, CAT IV 600 V
- Reversible holster for added protection of the display when not in use

## Product overview: Fluke 28 II Ex Intrinsically Safe True RMS Digital Multimeter

Now there's an intrinsically safe digital multimeter (DMM) you can use in a wide range of hazardous settings. Whether you work in petroleum, chemical, or pharmaceutical environments, the 28 II Ex gives high-end test and troubleshooting power you need is packed into the most rugged intrinsically safe (IS) DMM Fluke has ever built: drop-proof, waterproof, dust-proof (IP67). The 28 II Ex meets the following certifications:

.super-custom table { width: 80% !important; } .super-custom table, .super-custom table tbody, .super-custom table tr, .super-custom table tr td { border: none !important; } .super-custom table tr td { padding-bottom: 15px !important; } .super-custom table tr td p { margin-bottom: 5px !important; }

**IECEEx (International)**

- Ex ia IIC T4 Gb
- Ex ia I Ma


**ATEX (Europe)**

- II 2G Ex ia IIC T4 Gb
- I M1 Ex ia I Ma


**NEC / CEC (North America)**

- Class I, Division 1, Groups A,B,C,D T4
- Class I, Zone 1, AEx ia IIC T4
- Ex ia IIC T4


**PCEC (China)**

- Ex ia IIC T4 Gb


**Simtars (Australia)**

- Ex ia I Ma


**IEx (Brazil)**

- Ex ia IIC T4 Gb


**EAC (Russia)**

- 1Ex ia IIC T4 Gb X
- PO Ex ia I Ma X
- IP6X



## All the measurement functions of our most popular industrial DMMs

One tool equips you with all the testing and troubleshooting power you need wherever you go—inside or outside ATEX zones 1 or 2. No need to carry different meters for different areas, or worry about crossing through an Ex-required zone with a non-Ex rated instrument.

- 4-1/2 digit mode for precise measurements (20 000 counts)
- True-rms ac voltage and current for accurate measurement on nonlinear signals
- Measures up to 1000 V and 10A AC and DC (note that Ex zones require reduced measurements)
- Low pass filter ensures accurate voltage and frequency measurements on variable speed motor drives (VSDs)
- Frequency to 200 kHz and % duty cycle to help you diagnose VSDs and switching power supplies
- Resistance, continuity and diode test
- 10 000 µF capacitance range for components and motor caps
- Conductance measurements for high resistance or leakage tests
- Min/Max-Average and Peak capture to record transients and variations automatically
- Relative mode to remove test lead interference on resistance measurements
- Auto and manual ranging for maximum flexibility
- Input Alert protects you by chirping and flashing "Lead when leads are plugged into the wrong inputs"

## Easy to use

Important extras keep you productive all day long in less than optimal conditions.

- Backlit keypad buttons provide extra visibility in poorly lit areas, even when you're wearing full PPE
- Large display digits and 2-level bright white backlight also increases visibility
- Long battery life – 400 hours typical without backlight (Alkaline)
- Optional magnetic hanger for easy setup and viewing while freeing your hands for other tasks

## Easy to service in the field

Access to the separate battery compartment makes it easy to change batteries or fuses without jeopardizing instrument calibration.

## Specifications: Fluke 28 II Ex Intrinsically Safe True RMS Digital Multimeter

### Accuracy Specifications

Accuracy specifications are shown as  $\pm(\% \text{ of reading} + \text{number of digits})$

DC voltage	Range	0.1 mV to 1000 V
	Accuracy	$\pm(0.05\% + 1)$
AC voltage	Range	0.1 mV to 1000 V
	Accuracy	$\pm(0.7\% + 4)$
DC current	Range	0.1 $\mu$ A to 10 A
	Accuracy	$\pm(0.2\% + 4)$
AC current	Range	0.1 $\mu$ A to 10 A
	Accuracy	$\pm(1\% + 2)$
Resistance	Range	0.1 $\Omega$ to 50 M $\Omega$
	Accuracy	$\pm(0.2\% + 1)$
Conductance	Range	60.00 nS
	Accuracy	$\pm(1.0\% + 10)$
Diode test	Range	2.0 V
	Accuracy	$\pm(2.0\% + 1)$
Duty cycle	Range	0.0% to 99.9%
	Accuracy	Within $\pm(0.2\% \text{ per kHz} + 0.1\%)$ for rise times $<1 \mu$ s
Capacitance	Range	10 nF to 9999 $\mu$ F
	Accuracy	$\pm(1\% + 2)$
Frequency	Range	0.5 Hz to 199.99 kHz
	Accuracy	$\pm(0.005\% + 1)$

Temperature	Range	-200°C to +1090°C (-328°F to +1994°F)
	Accuracy	±(1% + 10)°C [±(1% + 10)°F]
Display counts	6000 counts/19,999 counts in high-resolution mode	
Peak capture	Record transients up to 250 us	
Min/Max/Avg recording	Display signals up to approximately 100 ms	
Accuracy specifications are shown as ±(% of reading + number of digits)		
Safety Certifications		
ATEX	{Ex} II 2G Ex ia IIC T4 Gb	
	{Ex} I M1 Ex ia I Ma	
NEC-500	Class I, Div 1, Groups A-D, 130°C	
IECEEx	Ex ia IIC T4 Gb	
	Ex ia I Ma	
GOST R Ex	1Ex ia IIC T4 Gb X	
	PO Ex ia I Ma X	
	IP6X	
General Specifications		
Power	Three AAA batteries	
	Battery life: 400 hours	
Display	LCD, with backlight	
External protection	Rubber holster	
Warranty	Three years	
Size with holster (H x W x L)	6.4 x 10.0 x 19.8 cm (2.5 x 3.9 x 7.8 in)	
Weight with holster	700 g (1.54 lb)	

**Fluke.** *Keeping your world up and running.®*

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**For more information call:**  
In the U.S.A. (800) 443-5853  
In Canada (800) 36-FLUKE  
From other countries +1 (425) 446-5500  
[www.fluke.com](http://www.fluke.com)

©2023 Fluke Corporation.  
Specifications subject to change without notice.  
02/2023

**Modification of this document is not permitted  
without written permission from Fluke Corporation.**