



Part No. A1001011 Automotive GPS/GNSS (On/Off Ground) or ISM FR4 Antenna

1.561, 1.575, 1.603 GHz or 868-928 MHz

Supports: Tracking, Smart Home, Agriculture, Automotive, Healthcare, Digital Signage, Wearables, Industrial Devices



*ISM layout offered in Appendix 1 Automotive GPS / GLONASS / Beidou / Galileo FR4 Antenna

1.559 – 1.610 GHz or ISM 868 – 928 MHz

KEY BENEFITS Stay-in-Tune

IMD antenna technology provides superior RF field containment, resulting in less interaction with surrounding components.

Quicker Time-to-Market

By optimizing antenna size, performance and emissions, customer and regulatory specifications are more easily met.

Reliability

Products are the latest RoHS version compliant.

APPLICATIONS

•	Embedded	•	Telematics
	design	•	Tracking
•	Cellular,	•	Healthcare
	Headsets,	•	M2M,
	Tablets		Industrial
•	Gateway,		devices
	Access Point	•	Smart Grid
•	Handheld	•	OBD-II

KYOCERA AVX A-Series automotive antennas deliver on the key needs of device designers for higher functionality.

KYOCERA AVX has completed rigorous testing to qualify the A-series antennas for automotive applications. Although the AEC-Q200 standard does not include antenna products, all testing has been done following applicable AEC-Q200 requirements and procedures as closely as possible. Customers must provide additional quality requirements, if any, to drive additional compliance testing. **Greater Flexibility**

KYOCERA AVX IMD technology enables the advance antenna design that delivers superior performance in reception critical applications. A1001011 is capable for off-ground and on-ground (over metal) environments. The A1001011 can also achieve ISM performance with proper layout shown on Appendix 1.

Electrical Specifications

Typical Characteristics, on 72 x 50 mm PCB

Frequency (GHz)	1.559 - 1.563	1.575	1.559 - 1.591	1.593 - 1.610	*868 – 928 MHZ
Mounting		Off Ground / On Ground			
GNSS Bands	Beidou	GPS	Galileo	Glonass	~ +
Peak Gain (dBi)	0.96 / -0.26	0.87 / -0.22	0.96 / -0.18	1.00 / -0.35	Refer to Albertaix 1
Efficiency (%)	72/47	71/46	70/45	69/41	Refer to
Center Frequency f₀ (GHz)	1.561	1.575	1.575	1.603	
VSWR		1.5:1	/ 2.5:1		
Feed Point Impedance		50 Ω un	balanced		

Mechanical Specifications & Ordering Part Number

Ordering Part Number	A1001011
Size (mm)	22.0 x 3.2 x 3.3
Mounting	SMT (P&P)
Weight (grams)	0.45
Packaging	Tape & Reel
Demo Board	1001011-02 (GNSS Demo Board)
	1001011-04 (ISM Demo Board)

Proprietary



Me	Mechanical Specifications & Ordering Part Number cont.				
	Ordering Part #	A1001011			
	Temperature Range	-50/+125 °C			
	Temperature Cycle	IEC 60068-2-14:2009			
	Temperature Exposure	Mil-STD-202 Method 108			
	High Temperature & High Humidity	MIL-STD-202			
	Mechanical Shock	IEC 60068-2-27:2008			
	Vibration	IEC 60068-2-6:2007			
	IMDS and PPAP available				




Antenna Dimensions


Typical antenna dimensions (mm)

Part Number	А	В	С
A1001011	22.0 ± 0.2	3.2 ± 0.1	3.3 ± 0.33










<u>Height</u>




Bottom View

TDS-ANT-0092 | Rev 0







Typical Performances on 72 x 50 mm PCB



Antenna Radiation Patterns (Off-Ground)

Typical Performances on 72 x 50 mm PCB measured @ 1.575 GHz







© 2022 KYOCERA AVX

TDS-ANT-0092 | Rev 0





9.75 21.85 22.34 23.12 23.57 24.35 13.23 6.33 0.00 0.15 0.15 3.25 69.6 9.79 0.00 0,15 Antenna D 0.85 3.05 Outline Pin #4 Pin #3 Pin #2 Pin #1 S1 SOLDER MASK PADS




Pin Descriptions


Pin#	Description
1	Feed
2	Dummy Pad
3	Dummy Pad
4	Dummy Pad


Matching Pi Network (Demo Board)

Component	Value	Tolerance
P1	DNI	N/A
S1	4.3pF	±0.25pF
P2	1pF	±0.5pF
P3	0Ω	N/A

*Actual matching values depend on customer design








© 2022 KYOCERA AVX


TDS-ANT-0092 | Rev 0






Typical Performances on 72 x 50 mm PCB






Antenna Radiation Patterns (On-Ground)

Typical Performances on 50 x 72 mm PCB measured @ 1.575 GHz







© 2022 KYOCERA AVX

TDS-ANT-0092 | Rev 0










Pin Descriptions


Pin#	Description
1	Feed
2	Dummy Pad
3	Dummy Pad
4	Dummy Pad


Matching Pi Network (Demo Board)

Component	Value	Tolerance
P1	2.4pF	±0.1pF
S1	0Ω	N/A
P2	DNI	N/A
P3	0Ω	N/A

*Actual matching values depend on customer design







BOTTOM METAL


© 2022 KYOCERA AVX

TDS-ANT-0092 | Rev 0



Antenna Demo Board
1001011-02 Off-Ground

Part Number	A (mm)	B (mm)	C (mm)
1001011-02	72.0	50.0	15.0





<u>Appendix 1</u>


Appendix 1 gives instructions on how to match antenna through impedance matching network for ISM (868-928 MHz) only.

Frequency (MHz)	868 - 928
Mounting	Off Ground
Peak Gain (dBi)	1.0
Efficiency (%)	64
VSWR	<2.5:1
Feed Point Impedance	50 Ω unbalanced


*Data shown above has Appendix 1 matching applied on 115 x 26.5 mm pcb.

Part Number	A (mm)	B (mm)
1001011-04	26.5	115.0

*Appendix 1 Antenna Demo Board







* VIAS: Diam. 0.2mm, (no vias on transmission lines). Via holes must be covered by solder mask


Pin Descriptions


Pin#	Description
1	Feed
2	Dummy Pad
3	Dummy Pad
4	Dummy Pad

Matching Pi Network (Demo Board)

Component	Value	Tolerance	Board Label
P1	DNI	N/A	
S1	0Ω	N/A	
P2	18nH	±2%	F6
S2	0Ω	N/A	E1
S3	0Ω	N/A	D18
S4	DNI	N/A	C17

*Actual matching values depend on customer design






© 2022 KYOCERA AVX

TDS-ANT-0092 | Rev 0




Appendix 1 ISM Antenna Tuning Structure (Off-Ground)

Typical layout dimensions (mm)



Component	Value	Tolerance	Board Label
P1	DNI	N/A	
S1	0Ω	N/A	
P2	18nH	±2%	F6
S2	0Ω	N/A	E1
S 3	0Ω	N/A	D18-D2
S4	DNI	N/A	C17

S1-+



0Ω

© 2022 KYOCERA AVX

TDS-ANT-0092 | Rev 0

S4

tel +(1) 858.550.3820 email: antenna.info@kyocera-avx.com 1 Avx Blvd, Fountain Inn, SC 29644


N/A


C17-C1



VSWR and Efficiency Plots (ISM Off-Ground)

Typical Performances on 115 x 26.5 mm PCB







Antenna Radiation Patterns (ISM Off-Ground)

Typical Performances on 115 x 26.5 mm PCB measured @ 870, 910 MHZ

870 MHz 910 MHz





© 2022 KYOCERA AVX

TDS-ANT-0092 | Rev 0