



## Product Change Notification / ASER-02NIOC250

---

**Date:**

07-Feb-2023

**Product Category:**

Motor Drivers, Power Management - PWM Controllers, Power MOSFET Drivers

**PCN Type:**

Manufacturing Change

**Notification Subject:**

CCB 6136 Final Notice: Qualification of MMT as an additional assembly site for selected MIC460xx, MIC410xx and MIC380xx device families available in 8L SOIC (3.90mm) package.

**Affected CPNs:**

[ASER-02NIOC250\\_Affected\\_CPN\\_02072023.pdf](#)  
[ASER-02NIOC250\\_Affected\\_CPN\\_02072023.csv](#)

**Notification Text:**

**PCN Status:**Final Notification

**PCN Type:**Manufacturing Change

**Microchip Parts Affected:**Please open one of the files found in the Affected CPNs section.  
Note: For your convenience Microchip includes identical files in two formats (.pdf and .xls)

**Description of Change:**Qualification of MMT as an additional assembly site for selected MIC460xx, MIC410xx and MIC380xx device families available in 8L SOIC (3.90mm) package.

**Pre and Post Change Summary:**

	Pre Change	Post Change
--	------------	-------------

Assembly Site	Stars Microelectronics (Thailand) Public Company Limited (STAR)	Unisem (M) Berhad Perak, Malaysia (UNIS)	Stars Microelectronics (Thailand) Public Company Limited (STAR)	Unisem (M) Berhad Perak, Malaysia (UNIS)	Microchip Technology Thailand (MMT)
Wire Material	Au	Au	Au	Au	Au
Die Attach Material	2200D	8290	2200D	8290	8390A
Molding Compound Material	G600	G600KA	G600	G600KA	G600V
Lead-Frame Material*	A194/CDA194	A194	A194/CDA194	A194	CDA194
Lead-Frame Paddle Size	95x130	95x130	95x130	95x130	95x130
DAP Surface Prep	NiPdAu	NiPdAu	NiPdAu	NiPdAu	Bare Cu

\*Note: C194, A194 or CDA194 Lead-Frame material are the same, it is just a MCHP internal labelling difference.

**Impacts to Data Sheet:**None

**Change Impact:**None

**Reason for Change:**To improve cycle time and productivity by qualifying MMT as an additional assembly site.

**Change Implementation Status:**In Progress

**Estimated First Ship Date:**March 2, 2023 (date code: 2309)

Note: Please be advised that after the estimated first ship date customers may receive pre and post change parts.

**Time Table Summary:**

	February 2023				March 2023				
	5	6	7	8	9	10	11	12	13
Workweek									
Qual Report Availability		x							
Final PCN Issue		x							

Date									
Estimated Implementation Date					X				

**Method to Identify Change:**Traceability code

**Qualification Report:**Please open the attachments included with this PCN labeled as PCN\_#\_Qual\_Report.

**Revision History:**February 7, 2023: Issued final notification.

The change described in this PCN does not alter Microchip’s current regulatory compliance regarding the material content of the applicable products.

### Attachments:

- [PCN ASER-02NIOC250\\_Qual Report.pdf](#)
- [PCN\\_ASER-02NIOC250\\_Pre and Post Change Summary.pdf](#)

Please contact your local [Microchip sales office](#) with questions or concerns regarding this notification.

### Terms and Conditions:

If you wish to receive Microchip PCNs via email please register for our PCN email service at our [PCN home page](#) select register then fill in the required fields. You will find instructions about registering for Microchips PCN email service in the [PCN FAQ](#) section.

If you wish to change your PCN profile, including opt out, please go to the [PCN home page](#) select login and sign into your myMicrochip account. Select a profile option from the left navigation bar and make the applicable selections.

Affected Catalog Part Numbers (CPN)

MIC4605-1YMVAO  
MIC4605-2YMVAO  
MIC4605-1YM-TRVAO  
MIC4605-2YM-TRVAO  
MIC4100YM  
MIC4101YM  
MIC4102YM  
MIC4103YM  
MIC4104YM  
MIC4100YM-TR  
MIC4101YM-TR  
MIC4102YM-TR  
MIC4103YM-TR  
MIC4104YM-TR  
MIC3808YM  
MIC3809YM  
MIC3808YM-TR  
MIC3809YM-TR  
MIC4605-1YM  
MIC4605-2YM  
MIC4605-1YM-TR  
MIC4605-1YM-T5  
MIC4605-2YM-TR  
MIC4605-2YM-T5  
MIC4604YM  
MIC4604YM-TR  
MIC4604YM-T5



**MICROCHIP**

**QUALIFICATION REPORT SUMMARY**  
**RELIABILITY LABORATORY**

PCN #: ASER-02NIOC250

Date:  
January 10, 2023

Qualification of MMT as an additional assembly site for selected MIC460xx, MIC410xx and MIC380xx device families available in 8L SOIC (3.90mm) package. This is a qualification by similarity.



## **MICROCHIP PACKAGE QUALIFICATION REPORT**

<b>Purpose</b>	Qualification of MMT as an additional assembly site for selected MIC460xx, MIC410xx and MIC380xx device families available in 8L SOIC (3.90mm) package. This is a qualification by similarity.
<b>CCB</b>	5125 & 6136
<b>CN</b>	E000116907
<b>QUAL ID</b>	R2201027 Rev. A
<b>MP CODE</b>	27812YC2XVA1
<b>Part No.</b>	MIC4604YM-TRVAO
<b>Bonding No.</b>	BD-000602 Rev.01
<b><u>Package</u></b>	
<b>Type</b>	8L SOIC
<b>Package size</b>	150 mils (3.90mm)
<b><u>Lead Frame</u></b>	
<b>Paddle size</b>	95 x 130 mils
<b>Material</b>	CDA194
<b>Surface</b>	Bare Cu
<b>Process</b>	Stamp
<b>Lead Lock</b>	No
<b>Part Number</b>	10100819
<b>Treatment</b>	BOT
<b><u>Material</u></b>	
<b>Epoxy</b>	8390A
<b>Wire</b>	Au wire
<b>Mold Compound</b>	G600V
<b>Plating Composition</b>	Matte Sn



# MICROCHIP PACKAGE QUALIFICATION REPORT

## Manufacturing Information

Assembly Lot No.	Wafer Lot No.	Date Code
MMT-231301242.000	TMPE220224873.300	2226V33
MMT-231301360.000	TMPE220224873.300	2226YR9
MMT-231400767.000	TMPE220224873.300	2226YTR

## Result

Pass     Fail     \_\_\_\_\_

8L SOIC (150 mils) assembled by MMT pass reliability test per QCI-39000.  
This package was qualified the Moisture/Reflow Sensitivity Classification Level 1 at 260°C  
reflow temperature per IPC/JEDEC J-STD-020E standard.

# PACKAGE QUALIFICATION REPORT

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS	Result	Remarks
<u>Precondition</u> <u>Prior Perform</u> <u>Reliability Tests</u> (At MSL Level 1)	<b>Electrical Test:</b> +25°C, 85°C and 125°C System: TMT	JESD22-A113	693(0)	0/693		Good Devices
	Bake 150°C, 24 hrs System: CHINEE	JIP/ IPC/JEDEC J-STD-020E		0/693		
	85°C/85%RH Moisture Soak 168 hrs. System: TABAI ESPEC Model PR-3SPH			0/693		
	3x Convection-Reflow 265°C max System: Vitronics Soltec MR1243			0/693		
	<b>Electrical Test:</b> +25°C, 85°C and 125°C System: TMT		693(0)	0/693	Pass	



# PACKAGE QUALIFICATION REPORT

Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS.	Result	Remarks
<b>Temp Cycle</b>	<b>Stress Condition:</b> -65°C to +150°C, 500 Cycles System: TABAI ESPEC TSA-70H	JESD22-A104		0/231		Parts had been pre-conditioned at 260°C 77 units / lot
	<b>Electrical Test:</b> +85°C and 125°C System: TMT		231(0)	0/231	Pass	
	<b>Bond Strength:</b> Wire Pull (>6.00 grams) Bond Shear (>22.00 grams)		15(0)	0/15	Pass	
<b>UNBIASED-HAST</b>	<b>Stress Condition:</b> +130°C/85%RH, 96 hrs. System: HAST 6000X	JESD22-A118		0231		Parts had been pre-conditioned at 260°C 77 units / lot
	<b>Electrical Test:</b> +25°C System: TMT		231(0)	0/231	Pass	
<b>HAST</b>	<b>Stress Condition:</b> +130°C/85%RH, 96 hrs. <b>Bias Volt:</b> 16 Volts System: HAST 6000X	JESD22-A110		231		Parts had been pre-conditioned at 260°C 77 units / lot
	<b>Electrical Test:</b> +25°C, 85°C and 125°C System: TMT		231(0)	0/231	Pass	

## PACKAGE QUALIFICATION REPORT


Test Number (Reference)	Test Condition	Standard/ Method	Qty. (Acc.)	Def/SS.	Result	Remarks
<b>High Temperature Storage Life</b>	<b>Stress Condition:</b> Bake 175°C, 500 hrs. System: SHEL LAB	JESD22- A103		0/45		
	<b>Electrical Test:</b> +25°C, 85°C and 125°C System: TMT		45(0)	0/45	Pass	
<b>Solderability Temp 215°C</b>	<b>Steam Aging:</b> Temp 93°C,8Hrs System: SAS-3000 Solder Dipping: Solder Temp.215°C Solder material: SnPb Sn63, Pb37 System: ERSA RA 2200D Visual Inspection: External Visual Inspection	J-STD-002	22(0)	0/22		
				0/22		
				0/22	Pass	
<b>Solderability Temp 245°C</b>	<b>Steam Aging:</b> Temp 93°C,8Hrs System: SAS-3000 Solder Dipping:Solder Temp.245°C Solder material:Pb Free Sn 95.5Ag3.9 Cu0.6 System: ERSA RA 2200D Visual Inspection: External Visual Inspection	J-STD-002	22(0)	0/22		
				0/22		
				0/22	Pass	
<b>Physical Dimensions</b>	Physical Dimension, 10 units / 1 lot	JESD22- B100/B108	30(0) Units	0/30	Pass	
<b>Bond Strength Data Assembly</b>	Wire Pull (>6.00 grams)	Mil. Std. 883-2011	30(0) Wires	0/30	Pass	
	Bond Shear (>22.00 grams)	CDF-AEC- Q100-001	30(0) bonds	0/30	Pass	

**CCB 6136**  
**PCN #: ASER-02NIOC250**







---

A Leading Provider of Smart, Connected and Secure Embedded Control Solutions



SMART | CONNECTED | SECURE

# Pre and Post Summary – Bondshell Comparison

STAR		UNIS		MMT	
	<b>Lead-Frame Material</b> A194				
	<b>Lead-Frame Material</b> CDA194	<b>Lead-Frame Material</b>	A194	<b>Lead-Frame Material</b>	CDA194

Note: C194, A194 or CDA194 Lead-Frame material are the same, it is just a MCHP internal labelling difference.