



Description

This thermometer is microprocessor-based, digital thermometer designed to use external J-, K-, T-, E-, R-, S- and N- type thermocouples as temperature sensors. This model is a dual input (T1, T2) suitable for K-, J-, T-, E-, R-, S- and N- type thermocouples. Equipped with over limit alarm, over limit signal output and user self-debug features.

Features

°C/°F/K Selection

- Data Hold
- Auto Power Off
- Low Battery Indication
- MAX Mode
- MIN Mode
- AVG Mode
- Data Logging : 100
- USB Interface
- High Alarm
- Lower Alarm
- High/Lower Signal Output
- LCD Backlight
- Auto Calibration
- Electricity Cut-off Memory

Specifications

Single or Dual Input		Range	Dual Accuracy
Temperature	Туре К	-200°C to 1372°C(-328°F to 2501°F)	±(0.2%+0.6)
	Type J	-210°C to 1200°C(-346°F to 2192°F)	±(0.2%+0.6)
	Туре Т	-250°C to 400°C(-418°F to 752°F)	±(0.2%+0.6)
	Type E	-150°C to 1000°C(-238°F to 1832°F)	±(0.2%+0.6)
	Type R	0.0°C to 1767°C(+32°F to 3212°F)	±(0.2%+2)
	Type S	0.0°C to 1767°C(+32°F to 3212°F)	±(0.2%+2)
	Type N	-200°C to 1300°C(-328°F to 2372°F)	±(0.2%+1.5)
Resolution		0.1°C (When Value > 999.9°C:1°C)	

General Characteristic

Power	USB or 9V Battery (6F22)	
LCD Size	30mm × 32mm	
Product Colour	Orange and Grey	
Product Net Weight	270g	
Product Size	175mm × 85mm × 30mm	
Standard Accessories	Battery, USB Interface Cable, Type K Temperature Probe	

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk www.mcmelectronics.com



2 Channel Thermometer



Type K Temperature Probe

Selection of Materials:

- 1. The cable sheath material: PTFE accord with the EU ROHS directive released by the blue.
- 2. Plugs material: ABS yellow
- 3. ALPHA green solder wire; Environmental protection neutral solder paste in accordance with the EU ROHS directive released
- 4. Nickel chrome Nickel alloy wire silicon symbol national class I standard GB 2614-1998 T

Test Range: -40°C to 800°C

Permissible error: Thermocouple allowed error of plus or minus 4% t (t for measuring temperature), such as 50 degrees $0.4\% \times 50 = 0.2$

Nickel chrome - Nickel alloy wire silicon chemical composition: the anode (KP) in the name of the chemical composition is: Ni, Cr = 90:10, the cathode (KN) chemical composition as follows: in the name of the Ni: Si = 97

- 5. Thermocouple exposed length: 5 +4/0mm
- 6. Temperature probe size chart:



Part Number Table

Description	Part Number
2 Channel Thermometer	72-7715

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com www.farnell.com www.newark.com www.cpc.co.uk www.mcmelectronics.com

