

Datasheet

IEC Glassfibre Thermocouple Cable with Stainless Steel Overbraid Extension Leads with Miniature Thermocouple Plugs & Sockets

Fitted with cable clamps



Cable Description

- Glassfibre insulated extension cable with stainless steel overbraiding
- Thermocouple types K in lengths 5m
- 7/0.2mm stranded conductors
- Glassfibre insulated flat pair construction, conductors laid flat, Glassfibre insulated with Glassfibre jacket, silicone varnished throughout + stainless steel overbraid for added protection and mechanical strength
- Good temperature resistance but not suitable where fluids are present
- Cable clamp fitted for securing cable to plugs
- Tolerance Class 2 to IEC-584
- Insulation rating -60°C to 350°C (short periods up to 400°C)
- Colour code (cores & jacket) to IEC-584-3

Connector Description

- All contacts are polarised to ensure correct connection
- Cable clamp available for securing cable to plugs
- Types K contacts are made from true Thermocouple alloys
- Colour coded in accordance with IEC specification
- Maximum continuous operating temperature 220°C

Type	Length	Connector Size	Description	Order Number
K	5	Miniature	EXT-K-C4-5.0-MP-MS	XF-1854-FAR