



SAFETY DATA SHEET PETROL INJECTOR CLEANER

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name	PETROL INJECTOR CLEANER
Product number	QPI300, PPI306, SPI300, CCI300, SPI301, ZPI306
UFI	UFI: FCGR-HSA8-JK4M-5M8M

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Fuel additive.
-----------------	----------------

1.3. Details of the supplier of the safety data sheet

Supplier	TETROSYL EUROPE 79 rue du chemin vert 59.273 Fretin TEL: 03 20 28 06 30 qualite@tetrosyl-france.com
----------	---

Manufacturer	TETROSYL LIMITED Bury Lancashire England BL9 7NY 0161 764 5981 0161 797 5899 info@tetrosyl.com
--------------	---

1.4. Emergency telephone number

Emergency telephone	+44 (0)161 764 5981 (24 hrs)
---------------------	------------------------------

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (SI 2019 No. 720)

Physical hazards	Not Classified
Health hazards	Asp. Tox. 1 - H304
Environmental hazards	Not Classified

2.2. Label elements

Hazard pictograms



Signal word	Danger
Hazard statements	H304 May be fatal if swallowed and enters airways.

PETROL INJECTOR CLEANER

Precautionary statements

P101 If medical advice is needed, have product container or label at hand.
 P102 Keep out of reach of children.
 P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor.
 P331 Do NOT induce vomiting.
 P405 Store locked up.
 P501 Dispose of contents/ container in accordance with national regulations.

Supplemental label information

EUH066 Repeated exposure may cause skin dryness or cracking.

UFI

UFI: FCGR-HSA8-JK4M-5M8M

Contains

DISTILLATES (PETROLEUM), HYDROTREATED LIGHT; KEROSENE - UNSPECIFIED, HYDROCARBONS, C10-C13, N-ALKANES, ISOALKANES, CYCLICS, <2% AROMATICS

2.3. Other hazards

Not applicable.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

DISTILLATES (PETROLEUM), HYDROTREATED LIGHT; KEROSENE - UNSPECIFIED	60-100%
CAS number: —	EC number: 926-141-6
Repeated exposure may cause skin dryness or cracking.	
Classification	
Asp. Tox. 1 - H304	
HYDROCARBONS, C10-C13, N-ALKANES, ISOALKANES, CYCLICS, <2% AROMATICS	3-<5.0%
CAS number: —	EC number: 918-481-9
UK REACH registration number: UK-01-0468758243-9-0000	
Repeated exposure may cause skin dryness or cracking.	
Classification	
Flam. Liq. 3 - H226	
Asp. Tox. 1 - H304	
PHENOL, (DIMETHYLAMINO)METHYL-, POLYISOBUTYLENE DERIVS.	3-<5.0%
CAS number: —	EC number: 937-027-0
Classification	
Aquatic Chronic 3 - H412	

PETROL INJECTOR CLEANER

1,2,4-TRIMETHYLBENZENE		<0.1
CAS number: 95-63-6	EC number: 202-436-9	
Classification Flam. Liq. 3 - H226 Acute Tox. 4 - H332 Skin Irrit. 2 - H315 Eye Irrit. 2 - H319 STOT SE 3 - H335 Aquatic Chronic 2 - H411		
NAPHTHALENE		-<0.05
CAS number: 91-20-3	EC number: 202-049-5	
M factor (Acute) = 1	M factor (Chronic) = 1	
Classification Flam. Sol. 2 - H228 Acute Tox. 4 - H302 Carc. 2 - H351 Aquatic Acute 1 - H400 Aquatic Chronic 1 - H410		

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Remove affected person from source of contamination. Keep the affected person warm and at rest. Get prompt medical attention.
Inhalation	Get medical attention if any discomfort continues. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Get medical attention. Symptoms of lung oedema (shortness of breath) may develop up to 24 hours after exposure. Show this Safety Data Sheet to the medical personnel.
Ingestion	Rinse mouth thoroughly with water. Give plenty of water to drink. Get medical attention if a large quantity has been ingested. Show this Safety Data Sheet to the medical personnel.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water. Rinse with water. Get medical attention if irritation persists after washing.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Do not rub eye. Get medical attention promptly if symptoms occur after washing.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure. Effects may be delayed. Keep affected person under observation.
Inhalation	No specific symptoms known.
Ingestion	May cause discomfort if swallowed. May cause stomach pain or vomiting.
Skin contact	Skin irritation. Prolonged or repeated contact with skin may cause irritation, redness and dermatitis. Blistering may occur.

PETROL INJECTOR CLEANER

Eye contact Irritating to eyes. Symptoms following overexposure may include the following: Redness. Pain. May cause blurred vision and serious eye damage.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor No specific recommendations. If in doubt, get medical attention promptly.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Extinguish with the following media: Foam, carbon dioxide or dry powder. Water. Use fire-extinguishing media suitable for the surrounding fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards No specific precautions due to the small quantities handled. No unusual fire or explosion hazards noted.

Hazardous combustion products Oxides of carbon. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting No specific firefighting precautions known.

Special protective equipment for firefighters Leave danger zone immediately.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions For personal protection, see Section 8. In case of spills, beware of slippery floors and surfaces. Avoid contact with eyes and prolonged skin contact. Provide adequate ventilation. Avoid inhalation of spray mist and contact with skin and eyes.

6.2. Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground. Collect and dispose of spillage as indicated in Section 13.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Stop leak if possible without risk. Eliminate all sources of ignition. No smoking, sparks, flames or other sources of ignition near spillage. Provide adequate ventilation. Absorb spillage with non-combustible, absorbent material. Collect and place in suitable waste disposal containers and seal securely.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. For waste disposal, see section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Good personal hygiene procedures should be implemented. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site. Avoid eating, drinking and smoking when using the product. Avoid contact with skin and eyes. Do not handle broken packages without protective equipment.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Keep containers upright. Store in tightly-closed, original container. Keep away from heat, sparks and open flame.

PETROL INJECTOR CLEANER

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

No exposure limits known for ingredient(s).

1,2,4-TRIMETHYLBENZENE

Long-term exposure limit (8-hour TWA): WEL 25 ppm 125 mg/m³

Short-term exposure limit (15-minute): WEL

NAPHTHALENE

Long-term exposure limit (8-hour TWA): 10 53

Short-term exposure limit (15-minute): 15 80

WEL = Workplace Exposure Limit.

HYDROCARBONS, C10-C13, N-ALKANES, ISOALKANES, CYCLICS, <2% AROMATICS

DNEL General population - Oral; Long term systemic effects: 18.75 mg/kg/day

HYDROCARBONS, C10, AROMATICS, >1% NAPHTHALENE

DNEL Workers - Dermal; Long term systemic effects: 0.95 mg/kg
 Workers - Inhalation; Long term systemic effects: 2.31 mg/m³
 General population - Dermal; Long term systemic effects: 0.28 mg/kg
 General population - Inhalation; Long term systemic effects: 0.69 mg/m³
 General population - Oral; Long term systemic effects: 2.1 mg/kg
 General population - Oral; Long term systemic effects: 4.23 mg/kg

PNEC marine water; 0.001 mg/l
 Fresh water; 0.001 mg/l

DISTILLATES, HYDROTREATED HEAVY PARAFFINIC <3% DMSO EXTRACT (IP 346) (CAS: 64742-54-7)

DNEL Workers - Inhalation; Long term systemic effects: 2.73 mg/m³
 Workers - Dermal; Long term systemic effects: 0.97 mg/kg
 General population - Oral; Long term systemic effects: 0.74 mg/kg
 Workers - Inhalation; Long term local effects: 5.58 mg/m³
 General population - Inhalation; Long term local effects: 1.19 mg/m³

NAPHTHALENE (CAS: 91-20-3)

DNEL Workers - Dermal; Long term systemic effects: 3.57 mg/kg
 Workers - Inhalation; Long term local effects: 25 mg/m³
 Workers - Inhalation; Long term systemic effects: 25 mg/m³

PNEC Sediment (Freshwater); 0.0672 mg/kg
 Sediment (Marinewater); 0.0672 mg/kg
 STP; 2.9 mg/l
 Soil; 0.0533 mg/kg

8.2. Exposure controls

PETROL INJECTOR CLEANER

Protective equipment



Appropriate engineering controls

Provide adequate ventilation. Avoid inhalation of vapours and spray/mists. Observe any occupational exposure limits for the product or ingredients.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. It is recommended that gloves are made of the following material: Nitrile rubber. It should be noted that liquid may penetrate the gloves. Frequent changes are recommended.

Other skin and body protection

Wear appropriate clothing to prevent any possibility of skin contact. Provide eyewash station.

Hygiene measures

Provide eyewash station and safety shower. Wash contaminated clothing before reuse. Wash promptly with soap and water if skin becomes contaminated.

Respiratory protection

If ventilation is inadequate, suitable respiratory protection must be worn.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Clear liquid.
Colour	Yellow.
Odour	Organic solvents.
Melting point	Not determined.
Initial boiling point and range	175°C @
Flash point	80°C
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Not determined.
Vapour pressure	Not determined.
Vapour density	Not determined.
Relative density	0.805g/cm ³ @ 20°C
Solubility(ies)	Insoluble in water.
Partition coefficient	Not determined.
Auto-ignition temperature	Not determined.
Decomposition Temperature	Not determined.
Viscosity	<50 cP @ 20°C

9.2. Other information

Other information	None.
-------------------	-------

PETROL INJECTOR CLEANER

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity The following materials may react strongly with the product: Alkaline earth metals. Powdered metal.

10.2. Chemical stability

Stability No particular stability concerns.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions Not applicable.

10.4. Conditions to avoid

Conditions to avoid Avoid heat. Avoid contact with the following materials: Strong oxidising agents.

10.5. Incompatible materials

Materials to avoid Strong oxidising agents.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects No information available.

Acute toxicity - oral

Summary Not classified.

Acute toxicity - dermal

Summary Not classified.

Acute toxicity - inhalation

Summary Not classified.

Skin corrosion/irritation

Summary Not classified.

Serious eye damage/irritation

Summary Not classified.

Respiratory sensitisation

Summary Not classified.

Skin sensitisation

Summary Not classified.

Germ cell mutagenicity

Summary Not classified.

Carcinogenicity

Summary Not classified.

Reproductive toxicity

Summary Not classified.

PETROL INJECTOR CLEANER

Specific target organ toxicity - single exposure

Summary Not classified.

Specific target organ toxicity - repeated exposure

Summary Not classified.

Aspiration hazard

Summary Not classified.

Inhalation No specific health hazards known.

Ingestion May cause discomfort if swallowed.

Skin contact Prolonged and frequent contact may cause redness and irritation.

Eye contact May cause temporary eye irritation.

Acute and chronic health hazards No specific health hazards known. Because of the product's quantity and composition, the health hazard is regarded as low.

SECTION 12: Ecological information

Ecotoxicity The product contains a substance which is harmful to aquatic organisms and which may cause long-term adverse effects in the aquatic environment.

12.1. Toxicity

Toxicity Not considered toxic to fish.

Acute aquatic toxicity

Summary Not Classified

Acute toxicity - fish LC₅₀, 96 hours: 2200 (DISTILLATES (PETROLEUM), HYDROTREATED LIGHT; KEROSENE – UNSPECIFIED) mg/l, Fish

Acute toxicity - aquatic invertebrates Not available.

Chronic aquatic toxicity

Summary Not Classified

12.2. Persistence and degradability

Persistence and degradability There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

Partition coefficient Not determined.

12.4. Mobility in soil

Adsorption/desorption coefficient Not available.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This substance is not classified as PBT or vPvB according to current UK criteria.

12.6. Other adverse effects

Other adverse effects Not available.

PETROL INJECTOR CLEANER

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information	Waste should be treated as controlled waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.
Disposal methods	Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. Confirm disposal procedures with environmental engineer and local regulations.

SECTION 14: Transport information

General	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).
----------------	--

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant
No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments	NOTE: Lines within the margin indicate significant changes from the previous revision.
Issued by	Regulatory Department
Revision date	30/08/2022
Revision	26
Supersedes date	23/06/2022
SDS status	Approved.

PETROL INJECTOR CLEANER

Hazard statements in full

H226 Flammable liquid and vapour.
H228 Flammable solid.
H302 Harmful if swallowed.
H304 May be fatal if swallowed and enters airways.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H332 Harmful if inhaled.
H335 May cause respiratory irritation.
H351 Suspected of causing cancer.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.
H411 Toxic to aquatic life with long lasting effects.
H412 Harmful to aquatic life with long lasting effects.