



Handle for easy movement



360° rotation on vertical axis



3 settings for variable fan speed



360° rotation on horizontal axis



720° orbital air circulation coverage

ITEM. 05635

SIP 20" HEAVY-DUTY ORBITAL FLOOR FAN

MULTI-DIRECTIONAL ORBITAL FAN FOR POWERFUL INDOOR AIR CIRCULATION

PRODUCT OVERVIEW

The **SIP 20" Heavy-Duty Orbital Floor Fan** delivers powerful multi-directional airflow to help cool spaces and circulate air in a variety of indoor environments.

Mounted at four points on a steel tube frame, this heavy-duty 3-blade fan can be rotated and fixed between 720° on both its horizontal and vertical axis. This creates an orbital effect which maximises airflow coverage.

Fans are essential in helping to provide improved air quality to indoor spaces.

FEATURES & BENEFITS

✓ POWERFUL AIRFLOW

A heavy-duty 3-blade fan is powered from a 120w motor to deliver powerful and consistent airflow coverage.

✓ VARIABLE SPEED SETTINGS

Three settings for variable fan speed:

- Low: 900rpm
- Medium: 1100rpm
- High: 1300rpm

✓ ORBITAL AIRFLOW FUNCTION

The manually adjustable fan head can rotate 360° on its horizontal axis and 360° on its vertical axis to create 720° coverage of air circulation. The orbital effect created maximises airflow coverage for greater ventilation.

✓ OUTSTANDING MOBILITY

A sturdy and compact design allows the fan to be easily moved between locations for use.



**COMES WITH
A 2-YEAR
STANDARD
WARRANTY***

FIND OUT MORE AT
SIP-GROUP.COM/WARRANTY



For over 50 years, SIP Industrial Products Limited has been a flagship supplier of high-quality equipment and machinery to the ever-growing engineering, construction, automotive, and agricultural marketplaces.



ITEM. 05635

SIP 20" HEAVY-DUTY ORBITAL FLOOR FAN

OTHER FEATURES

✓ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.
A robust and balanced steel frame maintains fan stability when in use.

APPLICATIONS & USES

Delivers powerful variable speed air circulation to indoor spaces.

Perfect for industrial, commercial and agricultural workshop areas.

TECHNICAL INFORMATION

ITEM NO.	05635		
Input Supply	230v (13A)		
Motor Power	120w (0.16hp)		
Power Cable	180cm		
Fan Diameter	Ø 20" (508mm)		
Speed Settings	3 speed settings		
	Low	Medium	High
	900rpm	1100rpm	1300rpm
Noise Level	68dB(A)		
Net Weight	6.40kg		
Gross Weight	7.80kg		
Product Dimensions	695(H) x 665(W) x 258mm(D)		
Packaged Dimensions	765(H) x 710(W) x 270mm(D)		