


Easy-to-use-controls



Swivel drum for directional airflow



Wheel-mounted steel frame for outstanding mobility



Pull handle for easy movement



ITEM. 05636

# SIP 30" INDUSTRIAL DRUM FAN

**HEAVY-DUTY DRUM FAN FOR POWERFUL INDOOR AIR CIRCULATION**

## PRODUCT OVERVIEW

The **SIP 30" Industrial Drum Fan** delivers powerful, variable speed airflow to help cool spaces and freshen stale air in a variety of indoor industrial environments.

Wheel-mounted on a cradled steel frame, the drum enclosed, heavy-duty 3-blade fan can be rotated between 360° on its vertical axis to maximise air circulation and coverage.

Fans are essential in helping to provide improved air quality to indoor spaces.

## FEATURES & BENEFITS

### ✓ POWERFUL AIRFLOW

A heavy-duty 3-blade fan is powered from a 315w motor to deliver powerful and consistent airflow coverage.

### ✓ VARIABLE SPEED SETTINGS

Two settings for variable fan speed:

- Speed Setting 1: 880rpm
- Speed Setting 2: 960rpm

### ✓ DYNAMIC AIRFLOW FUNCTION

The adjustable tilting fan head can be rotated 360° on its vertical axis for greater airflow coverage.

### ✓ OUTSTANDING MOBILITY

The wheel-mounted, cradled steel frame is fitted with pull handles which allows the fan to be easily moved between locations for use.

### ✓ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.  
A robust and balanced steel frame maintains fan stability when in use.



**COMES WITH  
A 2-YEAR  
STANDARD  
SILVER  
WARRANTY\***

FIND OUT MORE AT  
[SIP-GROUP.COM/WARRANTY](http://SIP-GROUP.COM/WARRANTY)



For over 50 years, SIP Industrial Products Limited has been a flagship supplier of high-quality equipment and machinery to the ever-growing engineering, construction, automotive, and agricultural marketplaces.



ITEM. 05636

# SIP 30" INDUSTRIAL DRUM FAN

## APPLICATIONS & USES

Delivers powerful variable speed air circulation to indoor spaces.

Perfect for industrial, commercial and agricultural workshop areas.

## TECHNICAL INFORMATION

ITEM NO.	05636	
Input Supply	230v (13A)	
Motor Power	315w (0.42hp)	
Power Cable	185cm	
Fan Diameter	Ø 30" (785mm)	
Speed Settings	2 speed settings	
	Speed Setting 1	Speed Setting 2
	880rpm	960rpm
Noise Level	84dB(A)	
Net Weight	19.90kg	
Gross Weight	22.30kg	
Product Dimensions	900(H) x 875(W) x 300mm(D)	
Packaged Dimensions	940(H) x 955(W) x 285mm(D)	