

DATA SHEET

THP10 PLUG MOUNTED SOUS VIDE NEEDLE PROBE TYPE 'T'

PLUG MOUNTED NEEDLE PROBE - Type 'T'

Description

Needle probe plug mounted using a moulded connector.

Construction

Stainless Steel Needle probe plug mounted.
Needle is 3.3mm diameter, reduced to 1.5mm for approximately 10mm from tip and 100mm long.

Sensor Features

- **TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY.**

This probe is manufactured using a two stage moulding technique. Firstly the probes are encased in tough nylon, then a thermoplastic over moulding is applied. This gives an extremely robust and durable construction with the added benefit that the assembly is waterproof.

- **HIGH ACCURACY THERMOCOUPLE MATERIAL THROUGHOUT**

Type 'T' Thermocouple : ½ Class I (±0.25°C ±0.15%)

- **WIDE AMBIENT TEMPERATURE SPECIFICATION** : -30 TO 50 °C
- **TIME RESPONSE (96% of value in water)** : 1.6 Secs
- **MEASUREMENT RANGE** : -100 TO 250 °C

Cross-reference for compatible instruments

Suitable instruments for use with this probe

TME PART No	DESCRIPTION	APPLICATION
MM2000	SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT
MM2010	MAX / MIN HOLD INSTRUMENT	HIGH ACCURACY INSTRUMENT WITH MAX, MIN AND HOLD FEATURES
MM2020	DIFFERENTIAL INSTRUMENT	DUAL INPUT INSTRUMENT FOR DIFFERENTIAL MEASUREMENTS
MM2030	THERMOCOUPLE SIMULATOR	HIGH ACCURACY SIMULATOR WITH MEASUREMENT FACILITY
SOLO-T	COMPACT SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT