



TECHNICAL INFORMATION

Watts:	2
Lumens:	220
Unit Color:	Grey
Body Type:	PC + AL
LED Chip Type:	SMD-Samsung Chip
Dimmable:	No
Beam Angle:	170°
Color Temperature:	3000K
Dimension:	140x140x290mm
Detection Range:	3-5m
Battery Type:	Lithium 3.7V/2600mAh
Charging Time:	4-6 Hours
Working Time:	3-12 Hours
No. Of Led:	50
Solar Panel:	5.5V, 3W



FEATURES

- Solar Light built with highly efficient Samsung chips.
- Designed with sensor, offering 2 operation modes.
- Sensor Mode - Automatically turns on at dusk to 10% light & when motion detected turns 100% light On. Turns to 10% light when no motion detected & turns Off at dawn.
- Constant Brightness Mode - Automatically turns on at dusk to 100% light and works constantly till the battery capacity is reduced to zero.
- Solar powered zero electricity cost
- Easy to install(cordless) & low maintenance
- Suitable for Pathways, Garden, Patio and similar outdoor environment


SOLAR WALL LIGHTS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide an extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 21784 - 2 Grey

[View more details](#)



PACKAGING

Gross Weight (Kgs):	1.5
Unit CBM:	0.00856
Dimension:	140x140x290mm

MASTER BOX PACKAGING

Box Qty:	10
Length (Box) mm:	150
Width (Box) mm:	160
Height (Box) mm:	310

LISTING DETAILS

Commodity Code:	94054131
Ean Code:	3800157678773