

## | HYDRAULICS AND PNEUMATICS

### Background

Pneumatic technology is used in vehicle tires, air brakes of buses, trucks or trains, compressed-air engines, vacuum pumps and more. Hydraulic systems are used in vehicle braking systems, power steering systems, shock absorbers, material handling vehicles such as excavators and aerial work platforms, and more. Making sure the right gas or liquid pressure is administered to these systems is crucial, especially when we speak about hydraulics, where the liquid in the system

may be flammable. If the pressure or the temperature range are not correct, this can cause dangerous leaks and accidents.

*Pressure sensors maintain a constant output pressure of the gas or liquid, in order to avoid any leaks that could cause dangerous accidents.*

### Solution





Pressure sensors are used for pressure regulators, which match the demand for gas or liquid to the demands of the system, while maintaining a constant output pressure. Float switches make sure to keep the liquid level at an optimum level.

Position Sensors are used to monitor valves and actuators; "dual sensors" substantially reduce mounting and maintenance efforts through the combination of two sensors in one housing. Position sensors are available with terminals or cable connection, analog or IO-Link interface






## RECOMMENDED PRODUCTS

Reference on Diagram	Product	Features	Function
1	 <b>2CP5 Series</b>	<ul style="list-style-type: none"> <li>UL recognized ceramic capacitive sensor, overvoltage and short circuit protected; Durable, compact, low-cost design</li> </ul>	It measures the air pressure in the pneumatic system
2	 <b>PTE7100 PTE7300 Series</b>	<ul style="list-style-type: none"> <li>Ideal for mid and high pressure ranges</li> <li>Wide range of ports, connectors, and analog electrical outputs for ease of integration in various industrial applications</li> </ul>	Hydraulic and pneumatic system control
3	 <b>Hall Effect Rotary Position Sensor, IO-Link</b>	<ul style="list-style-type: none"> <li>Two-part design, modular, offering maximum flexibility during installation; IO-Link with COM3 transmission rate</li> </ul>	Permit to monitor valve opening
4	 <b>Industrial Pressure Transmitters</b>	<ul style="list-style-type: none"> <li>Excellent media compatibility, very stable electronics especially in high vibration and shock applications</li> </ul>	Monitor the air pressure supply to power pneumatic controls.



## FLUID MANAGEMENT APPLICATIONS



Sensata Technologies, Inc. ("Sensata") data sheets are solely intended to assist designers ("Buyers") who are developing systems that incorporate Sensata products (also referred to herein as "components"). Buyer understands and agrees that Buyer remains responsible for using its independent analysis, valuation, and judgment in designing Buyer's systems and products. Sensata data sheets have been created using standard laboratory conditions and engineering practices. Sensata has not conducted any testing other than that specifically described in the published documentation for a particular data sheet. Sensata may make corrections, enhancements, improvements, and other changes to its data sheets or components without notice.

Buyers are authorized to use Sensata data sheets with the Sensata component(s) identified in each particular data sheet. HOWEVER, NO OTHER LICENSE, EXPRESS OR IMPLIED, BY ESTOPPEL OTHERWISE TO ANY OTHER SENSATA INTELLECTUAL PROPERTY RIGHT, AND NO LICENSE TO ANY THIRD PARTY TECHNOLOGY OR INTELLECTUAL PROPERTY RIGHT, IS GRANTED HEREIN. SENSATA DATA SHEETS ARE PROVIDED "AS IS". SENSATA MAKES NO WARRANTIES OR REPRESENTATIONS WITH REGARD TO THE DATA SHEETS OR USE OF THE DATA SHEETS, EXPRESS, IMPLIED, OR STATUTORY, INCLUDING ACCURACY OR COMPLETENESS. SENSATA DISCLAIMS ANY WARRANTY OF TITLE AND ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, QUIET ENJOYMENT, QUIET POSSESSION, AND NON-INFRINGEMENT OF ANY THIRD PARTY INTELLECTUAL PROPERTY RIGHTS WITH REGARD TO SENSATA DATA SHEETS OR USE THEREOF.

All products are sold subject to Sensata's terms and conditions of sale supplied at [www.sensata.com](http://www.sensata.com) SENSATA ASSUMES NO LIABILITY FOR APPLICATIONS ASSISTANCE OR THE DESIGN OF BUYERS' PRODUCTS. BUYER ACKNOWLEDGES AND AGREES THAT IT IS SOLELY RESPONSIBLE FOR COMPLIANCE WITH ALL LEGAL, REGULATORY, AND SAFETY-ELATED REQUIREMENTS CONCERNING ITS PRODUCTS, AND ANY USE OF SENSATA COMPONENTS IN ITS APPLICATIONS, NOTWITHSTANDING ANY APPLICATIONS-RELATED INFORMATION OR SUPPORT THAT MAY BE PROVIDED BY SENSATA.

Mailing Address: Sensata Technologies, Inc., 529 Pleasant Street, Attleboro, MA 02703, USA

### Americas

Sensata Technologies Inc.  
529 Pleasant Street,  
Attleboro, MA 02703 USA  
pressure sensors & switches  
+1 (800) 350 2727  
[sensors@sensata.com](mailto:sensors@sensata.com)  
[switches@sensata.com](mailto:switches@sensata.com)  
Position Sensors and Encoders  
+1 (800) 350 2727  
[sales.beisensors@sensata.com](mailto:sales.beisensors@sensata.com)  
Cynergy3 Components  
+44 (0) 1202 897969  
[sales@cynergy3.com](mailto:sales@cynergy3.com)

### Europe, Middle East & Africa

Sensata Technologies Holland b.v.  
Jan Tinbergenstraat 80  
7559 SP Hengelo  
The Netherlands  
Pressure Sensors & switches  
+359 (2) 809 1826  
[pressure-info.eu@sensata.com](mailto:pressure-info.eu@sensata.com)  
Position Sensors and Encoders  
+33 (3) 88 20 8080  
[position-info.eu@sensata.com](mailto:position-info.eu@sensata.com)

## CONTACT US

Cynergy3 Components  
+44 (0) 1202 897969  
[sales@cynergy3.com](mailto:sales@cynergy3.com)

### Asia Pacific

Sensata Technologies china co., ltd.  
30th Floor, InterContinental Center,  
100 Yu Tong Rd, Jing An District, 200070  
Shanghai, China  
+86 (21) 2306 1500  
[sales.isasia@list.sensata.com](mailto:sales.isasia@list.sensata.com)  
Japan  
+81 (45) 277 7117  
[sales.isasia@list.sensata.com](mailto:sales.isasia@list.sensata.com)  
Korea  
+82 (31) 601 2004  
[sales.isasia@list.sensata.com](mailto:sales.isasia@list.sensata.com)  
India  
+91 (80) 67920890  
[sales.isasia@list.sensata.com](mailto:sales.isasia@list.sensata.com)  
Rest of Asia  
+886 (2) 27602006 ext 2808  
[sales.isasia@list.sensata.com](mailto:sales.isasia@list.sensata.com)  
Cynergy3 Components  
+44 (0) 1202 897969  
[sales@cynergy3.com](mailto:sales@cynergy3.com)