

MX-LED MX-LED MV and MX-LED 110/230V

Patent Pending / Registered Community Design / US Design Patent



CE – certified to EMC directive 2004/108/EC.
Complies with low voltage directive 2006/95/EC.
High voltage transient and polarity reversal protected.
Operating temperature: -20°C to + 55°C.



Mains 110/230V	amber > 15cd red > 25cd	65 flashes/min 6 bursts/flash	85–265 Vac	IP65	310gms
Multivoltage MV			10–100Vdc		

Features:

A bright LED beacon with low power consumption.

- Multivoltage 10–100Vdc, and mains 110Vac and 230Vac versions
- Unique patented design maximises light output
- Clear lens with coloured LEDs
- Low power consumption
- 3 year guarantee
- Weatherproof to IP65

Materials:

Polycarbonate lens and base. ROHS compliant.

Accessories:

FX9
protector
guard



FX14
mounting
bracket



Product	<i>i</i>	Amber	Red
Mains 110/230V	25mA @ 110Vac 15mA @ 230Vac	448052	448053
Multivoltage MV	230mA @ 12Vdc 110mA @ 24Vdc 60mA @ 50Vac 40mA @ 100Vac	446052	446053

106 mm

147 mm

Drilling for Panel Mounting (ISO 4148)

4 holes 7mm dia.

120°

120°

130 mm dia.

Cable entry