### AMP | AMP CPC

TE Internal #: 206708-1

Circular Power Connectors, Housing, 600 VDC, Wire-to-Wire, 9

Position, Wire & Cable, Plug, Socket, Power & Signal, Black, All

Plastic, AMP CPC

View on TE.com >



Connectors > Power Connectors > Circular Power > Circular Power Connectors > Circular Connector, Environmentally Sealed, CPC Series 6











Connector Product Type: Housing

Operating Voltage: 600 VDC

Connector System: Wire-to-Wire

Number of Positions: 9

Sealable: No

All Circular Connector, Environmentally Sealed, CPC Series 6 (19)

## **Features**

### **Product Type Features**

Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Plug
Circular Connector Shell Type	All Plastic

# **Configuration Features**

Reverse Numbering	Without
Number of Positions	9
Number of Power Positions	0
Number of Signal Positions	9

### **Electrical Characteristics**



Operating Voltage	600 VAC
Contact Features	
Reverse Gender	No
Contact Type	Socket
Contact Protection	With
Mechanical Attachment	
Mating Alignment Type	Keyed
Mating Alignment	With
Mating Retention Type	Threaded Coupling
Screw & Hole Thread Size	3/4 - 20 UNEF-2A
Polarization Code	A
Connector Mounting Type	Cable Mount (Free-Hanging)
Mating Retention	With
Panel Mount Feature	Without
Housing Features	
Body Orientation	Straight
Hausing Calar	Black
Housing Color	DIACK
Housing Color  Housing Material	Thermoplastic
Housing Material  Circular Connector Shell Size	Thermoplastic
Housing Material  Circular Connector Shell Size	Thermoplastic
Housing Material  Circular Connector Shell Size  Usage Conditions	Thermoplastic  13
Housing Material Circular Connector Shell Size  Usage Conditions  Operating Temperature Range  Fluid Resistance	Thermoplastic  13  -55 - 105 °C[-67 - 221 °F]
Housing Material Circular Connector Shell Size  Usage Conditions  Operating Temperature Range  Fluid Resistance	Thermoplastic  13  -55 - 105 °C[-67 - 221 °F]
Housing Material  Circular Connector Shell Size  Usage Conditions  Operating Temperature Range  Fluid Resistance  Operation/Application	Thermoplastic  13  -55 – 105 °C[-67 – 221 °F]  None
Housing Material  Circular Connector Shell Size  Usage Conditions  Operating Temperature Range  Fluid Resistance  Operation/Application  Circuit Application	Thermoplastic  13  -55 – 105 °C[-67 – 221 °F]  None  Power & Signal
Housing Material  Circular Connector Shell Size  Usage Conditions  Operating Temperature Range  Fluid Resistance  Operation/Application  Circuit Application  Shielded	Thermoplastic  13  -55 – 105 °C[-67 – 221 °F]  None  Power & Signal
Housing Material  Circular Connector Shell Size  Usage Conditions  Operating Temperature Range  Fluid Resistance  Operation/Application  Circuit Application  Shielded  Industry Standards	Thermoplastic  13  -55 – 105 °C[-67 – 221 °F]  None  Power & Signal  No
Housing Material  Circular Connector Shell Size  Usage Conditions  Operating Temperature Range  Fluid Resistance  Operation/Application  Circuit Application  Shielded  Industry Standards  UL Flammability Rating	Thermoplastic  13  -55 – 105 °C[-67 – 221 °F]  None  Power & Signal  No

# **Product Compliance**



#### For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-

# Compatible Parts



TE Part # CAT-AM71-C83998B CPC Cable Clamps



POWERBAND Contacts



CPC,13 LONG TUBE





TE Part # 81665-4 ECONOSEAL, FLANGE GASKET



TE Part # 211399-1 CPC PLUG ASSEMBLY SIZE 13-7



TE Part # CAT-AM71-C83998J Cable/Panel Mount Connector, CPC Series 1







TE Part # CAT-AM71-T98D
Pin and Socket Contacts, Type III, LP
EMEA



TE Part # CAT-AM71-T98A

Strip Pin and Socket Contacts, Type III,
LP



TE Part # CAT-AM71-T98G
Pin and Socket Contacts, Type III, LP,
High Current



TE Part # 211870-2 SEALING CAP ASSY,SZ 13,CPC



TE Part # CAT-AM71-T98
Pin and Socket Contacts, Type II



TE Part # CAT-AM71-T98B Strip Pin and Socket Contacts, Type III



TE Part # CAT-AM71-T98F Strip Pin and Socket Contacts, Type III, High Current



TE Part # CAT-AM71-C83998F Connectors with Posted Pin Contacts, CPC Series 1



TE Part # 91542-1
CCII TYPE III+ PIN SKT 24-22 ASSY



TE Part # 91515-1

CCII TYPE III+ MNL PIN SKT 30-20

ASSY



TE Part # 91519-1 CCII TYPE III+ PIN SKT 18-14 ASSY



TE Part # 91505-1 CCII TYPE III+ 24-16 ASSY

# Also in the Series | AMP CPC



Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)



Circular Connector Caps & Covers(16)



Circular Connector Hardware(3)



Circular Connector Keying Plugs(2)



Circular Connector Seals(36)




Circular Power Connectors(459)




Insertion & Extraction Tools(1)









# Customers Also Bought













## **Documents**

**Product Drawings** 

CPC PLUG ASSEMBLY SIZE 13-9

English

**CAD Files** 

3D PDF

3D

**Customer View Model** 

ENG\_CVM\_CVM\_206708-1\_S.2d\_dxf.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_206708-1\_S.3d\_igs.zip

English

**Customer View Model** 

ENG\_CVM\_CVM\_206708-1\_S.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.



## Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

**Product Specifications** 

**Application Specification** 

English

**Product Environmental Compliance** 

MD\_206708-1\_021920182242\_dmtec

English

MD\_206708-1\_021920182242\_dmtec

English

**Instruction Sheets** 

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English

**Agency Approvals** 

**UL Report** 

English