

Product Search Data Sheet

PRG18BB221MB1RB

In Production Recommended RoHS REACH

Appearance & Shape



e ++					
Dimensions (mm)					
Part Number	L	W	T	e	g
PRG03_RL	0.60±0.05	0.30±0.05	0.30±0.05	0.10 to 0.20	-
PRG15_RC	1.0±0.05	0.5±0.05	0.5±0.05	0.15 to 0.40	-
PRG18_RB	1.6±0.15	0.8±0.15	0.8±0.15	0.1 to 0.6	-
PRG21_RA	2.0±0.2	1.25±0.2	0.9±0.2	0.2 min.	0.5 min.
PRG21_RK	2.0±0.2	1.25±0.2	1.25±0.2	0.2 min.	0.5 min.

Note: This datasheet may be out of date. Please download the latest datasheet of PRG18BB221MB1RB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=PRG18BB221MB1RB

Features

1. Rapid operation to protect the circuit in an overcurrent condition abnormality such as a short circuit.

By removing the overcurrent condition, these products automatically return to the initial condition and can be used repeatedly.

2. Suitable for countermeasure to short circuit test in safety standard

3. Stable resistance after operation due to ceramic PTC

4. Similar size (0603 size) is possible due to the large capacity for electric power.

5. Possible to use these products as current limiting resistors with overcurrent protection functions

6. SMD type is helpful for miniaturizing circuits because of its small size and light weight

7. UL/cULcertified product.(UL1434, File No. E137188)



Applications

Limited Usage

Consumer Grade



Packaging Information

		Standard
Packaging	Specifications	Packing
		Quantity
RB	180mm Paper Tape	4000

1 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





PRG18BB221MB1RB

Note: This datasheet may be out of date. Please download the latest datasheet of PRG18BB221MB1RB from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-us/products/productdetail?partno=PRG18BB221MB1RB

Specifications

Max. Voltage	24V
Hold Current(25°C)	14mA
Measure Condition of Hold Current	(at +25°C)
Hold Current (2)	8mA
Measure Condition of Hold Current (2)	(at +75°C)
Trip Current(25°C)	29mA
Measure Condition of Trip Current	(at +25°C)
Trip Current(2)	37mA
Measure Condition of Trip Current(2)	(at -20°C)
Max. Current	130mA
Resistance (25°C)	220Ω
Resistance Value Tolerance (at 25°C)	±20%
Curie Point(typ.)	100°C
Operating Temperature Range	-20°C to 75°C
Size Code (in mm)	1.6x0.8mm
Size Code (in inch)	0.6x0.3inch
Shape	SMD
Mass	0.004g
MSL	1

2 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.






Product Search Data Sheet


PRG18BB221MB1RB

Note: This datasheet may be out of date. Please download the latest datasheet of PRG18BB221MB1RB from the official website of Murata Manufacturing Co., Ltd.


http://www.murata.com/en-us/products/productdetail?partno=PRG18BB221MB1RB

Product Data





Resistance-Temperature Charac.



Operating Time (Typical Curve)

Protective Threshold Current Range

3 of 3

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

