

Image for reference only

Features:

- Made in the UK
- A range of step-up/ step-down auto transformers
- 0-110-220-230-240V, 50/60Hz.
- Power ratings 50 ~ 5000VA
- Connection made by insulated terminal block
- Insulating rating: Class B
- Windings are covered with metal shrouds
- Custom design available




Description

Auto-transformers are suitable for applications where mains isolation is not essential.

The short term VA is indicated for applications of a intermittent load, generally for applications with an average intermittent work load of 50% . Example: supply to fridges, air conditioners, compressors etc..

Other ratings and voltages can be supplied on request.



*Note:
50VA has voltages
0-115-230

Schematic for reference

Selection Guide

Part No.	VA Rating	VA Max Short term	Dimension (mm)					Weight (Kgs)
			A	B	C	D	E	
VTX-186-50*	50	50	67	83	75	57	44	0.7
VTX-186-100	100	100	65	96	77	57	44	1.4
VTX-186-150	150	150	65	96	77	57	44	1.4
VTX-186-200	200	300	74	123	78	60	58	2.1
VTX-186-250	250	300	74	123	78	60	58	2.1
VTX-186-300	300	450	96	80	102	84	65	2.8
VTX-186-500	500	750	96	105	102	84	89	3.2
VTX-186-1000	1000	1500	120	120	124	90	106	6.3
VTX-186-2000	2000	3000	128	192	154	101	106	10.5
VTX-186-3000	3000	4500	195	202	180	160	140	13.5
VTX-186-5000	5000	7500	195	210	180	160	165	20

Please contact Vigortronix for any enquiries. Products can be altered to suit custom requirements. The information contained in this document is subject to change without notice.