

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product form : Mixture
Product name : RL420AR/NC
UFI : 16Y5-M0GA-Q003-70FG
Product code : RL420AR/NC
Type of product : Adhesives
Product group : Blend

1.2. Relevant identified uses of the substance or mixture and uses advised against**1.2.1. Relevant identified uses**

Main use category : Professional use
Industrial/Professional use spec : For professional use only
Use of the substance/mixture : Adhesives, binding agents
Function or use category : Adhesives, binding agents

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet**Supplier**

Robnor ResinLab Ltd
31 Athena Avenue
Elgin Industrial Estate
SN2 8EJ Swindon - United Kingdom
T +44(0) 1793 823741 - F +44(0) 1793 827033
eusds@robnor.co.uk

1.4. Emergency telephone number

Emergency number : +44(0) 1793 823741

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	Guy's & St Thomas' Poisons Unit Medical Toxicology Unit, Guy's & St Thomas' Hospital Trust	Avonley Road SE14 5ER	+44 20 7188 7188	

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No. 1272/2008 [CLP]**

Safety data sheet available on request. EUH210

Full text of H- and EUH-statements: see section 16

Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

2.2. Label elements**Labelling according to Regulation (EC) No. 1272/2008 [CLP]**

EUH-statements : EUH210 - Safety data sheet available on request.

2.3. Other hazards

Contains no PBT/vPvB substances $\geq 0.1\%$ assessed in accordance with REACH Annex XIII

RL420AR/NC

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
propylidynetrimethanol	(CAS-No.) 77-99-6 (EC-No.) 201-074-9	< 5	Repr. 2, H361

Full text of H- and EUH-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water. If skin irritation or rash occurs: Get medical advice/attention. Get medical advice if skin irritation persists.
First-aid measures after eye contact	: Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact : May cause an allergic skin reaction.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

Firefighting instructions	: Complete protective clothing. Prevent fire fighting water from entering the environment.
Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment. Do not allow to enter drains or water courses.

RL420AR/NC

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

6.3. Methods and material for containment and cleaning up

- Methods for cleaning up : Take up liquid spill into absorbent material.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Ensure good ventilation of the work station, ventilate curing ovens to prevent emissions in the workplace. Wear personal protective equipment.
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Store in a well-ventilated place. Keep cool. Keep container tightly closed. Store in original container.

7.3. Specific end use(s)

Adhesives, Sealants.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

No additional information available

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station, ventilate curing ovens to prevent emissions in the workplace.

Hand protection:

Protective gloves

Eye protection:

Safety glasses with side shields

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

Device	Filter type	Condition	Standard
Full face mask		If conc. in air > exposure limit	

Personal protective equipment symbol(s):



RL420AR/NC

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Color	: Colourless.
Odor	: Barely perceptible odour.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20°C	: No data available
Relative density	: 1.1
Solubility	: Soluble.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

VOC content : 0 %

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7). Keep away from heat.

10.5. Incompatible materials

Strong oxidizing agents. Strong acids. Strong bases.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

RL420AR/NC

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral) : Not classified (Based on available data, the classification criteria are not met)
Acute toxicity (dermal) : Not classified (Based on available data, the classification criteria are not met)
Acute toxicity (inhalation) : Not classified (Based on available data, the classification criteria are not met)

propylidyntrimethanol (77-99-6)	
LD50 oral rat	≈ 14700 mg/kg bodyweight Animal: rat, Animal sex: male
LD50 dermal rabbit	> 10000 mg/kg bodyweight Animal: rabbit
LC50 Inhalation - Rat	> 0.85 mg/l air Animal: rat, Animal sex: male

Skin corrosion/irritation : Not classified (Based on available data, the classification criteria are not met)
Serious eye damage/irritation : Not classified (Based on available data, the classification criteria are not met)
Respiratory or skin sensitisation : Not classified (Based on available data, the classification criteria are not met)
Germ cell mutagenicity : Not classified (Based on available data, the classification criteria are not met)
Carcinogenicity : Not classified (Based on available data, the classification criteria are not met)

Reproductive toxicity : Not classified (Based on available data, the classification criteria are not met)

STOT-single exposure : Not classified (Based on available data, the classification criteria are not met)

STOT-repeated exposure : Not classified (Based on available data, the classification criteria are not met)

propylidyntrimethanol (77-99-6)	
NOAEL (oral, rat, 90 days)	200 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)
NOAEC (inhalation, rat, gas, 90 days)	≈ 3.5 ppm Animal: rat

Aspiration hazard : Not classified (Based on available data, the classification criteria are not met)

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Hazardous to the aquatic environment, short-term (acute) : Not classified (Based on available data, the classification criteria are not met)
Hazardous to the aquatic environment, long-term (chronic) : Not classified (Based on available data, the classification criteria are not met)
Not rapidly degradable

propylidyntrimethanol (77-99-6)	
LC50 - Fish [1]	> 1000 mg/l Test organisms (species): Alburnus alburnus
LC50 - Fish [2]	> 10 g/l Test organisms (species): Alburnus alburnus
EC50 - Crustacea [1]	13000 mg/l Test organisms (species): Daphnia magna
EC50 72h - Algae [1]	> 1000 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
NOEC (chronic)	> 1000 mg/l Test organisms (species): Daphnia magna Duration: '21 d'

12.2. Persistence and degradability

No additional information available

RL420AR/NC

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

RL420AR/NC

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

Contains no substance(s) listed on the REACH Candidate List

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

VOC content : 0 %

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Abbreviations and acronyms:	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration

RL420AR/NC

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Full text of H- and EUH-statements:

EUH210	Safety data sheet available on request.
H361	Suspected of damaging fertility or the unborn child.
Repr. 2	Reproductive toxicity, Category 2

SDS EU (REACH Annex II) - EU date format

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.