



Construction

Specifications

No. of Outlets: 8 OutletsOutlet Type: UKCurrent Rating: 13ASupply Voltage: 250V ACPlug Type: UKPeak Surge Current: 4.5kA

Socket Base and Cover	: FRPP
Conductors (Bus bar)	: Brass
Cover Screw	: Mild Steel Nickel Plated
Switch	: Nylon House with Brass terminals
Shutter	: Nylon (PA)
Spring	: Mild Steel
Neon Lamp with 220kΩ Resistor	: Orange Light
Neon Lamp Cover	: Polycarbonate (PC)
Switch Rocker	: Polycarbonate (PC)
Surge Component	: Metal Oxide Varistor + thermal fuse + neon indicator (if applicable)
Plug	: 13A BS 1363 plug
Cable	: PVC, A05VV-F 3X1.25mm ²

Standard

BS 1363-2

Surge Protection Data

Voltage	: 220V – 240V
Operating Voltage (Vac rms)	: 300V Max.
Mains Three Way Protection	: LN LE NE
Peak Current (A)	: 4.5kA
Max. Energy (Joules)	: 3 x 125J
Max. Clamping Voltage	: 775Volts
Response Time (nS)	: <50ns

Part Number Table

Description	Part Number
Surge Protector, 8 Outlets, UK Type, 13A, UK, 2m	2818NS(1N) 2M

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-ELEC is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

