

groov EPIC® Processors

GRV-EPIC-PR1	Programmable automation controller, with Ignition 7
GRV-EPIC-PR2	Programmable automation controller, with increased RAM/storage & Ignition 8

groov EPIC Chassis

GRV-EPIC-CHS0	Processor and power supply only mounting chassis
GRV-EPIC-CHS4	4-module analog/digital/serial mounting chassis
GRV-EPIC-CHS8	8-module analog/digital/serial mounting chassis
GRV-EPIC-CHS16	16-module analog/digital/serial mounting chassis

groov EPIC Power Supplies

GRV-EPIC-PSAC	Power supply, 110–240 VAC
GRV-EPIC-PSDC	Power converter, 24–48 VDC
GRV-EPIC-PSPT	Pass-through power adapter, 11.4–12.6 VDC, up to 9 A

groov Analog Input Modules

GRV-IICTD-12	Analog input, temperature, ICTD, 12 channels
GRV-IMA-24	Analog input, 24 channels, configurable input ranges of 4–20 mA, 0–20 mA, ±20 mA
GRV-IMAI-8	Analog input, 0–20 mA, isolated, field or chassis-powered loop, 8 channels
GRV-ITM-12	Analog input, 12 channels, thermocouple or mV
GRV-ITMI-8	Analog input, 8 channels, thermocouple or mV, channel-to-channel isolation
GRV-IRTD-8	Analog input, temperature (RTD) or resistor, 8 channels
GRV-ITR-12	Analog input, 12 channels, temperature (thermistor) or resistor
GRV-IV-24	Analog voltage input, 24 channels, 8 configurable input ranges from ±1.25 V to ±160 VDC
GRV-IVAPM-3	Input, power monitoring, 3 phase, 600 VAC with 0.333 V, 1 V, or 5 A CT
GRV-IVI-12	Analog voltage input, 12 channels, configurable input ranges from ±1.25 to ±160 VDC, channel-to-channel isolation
GRV-IVIRMS-10	Analog RMS voltage input, 10 channels, 0-300 VAC/VDC, channel-to-channel isolation

groov Analog Output Modules

GRV-OVMALC-8	Analog output, 8 channels, voltage or current, chassis-powered loop
GRV-OVMAILP-8	Analog output, 8 channels, voltage or current, channel-to-channel isolation, field or chassis-powered loop

groov Discrete Input Modules

GRV-IAC-24	AC input, 24 channels, 85–140 VAC
GRV-IACS-24	AC input, 24 channels, 85–140 VAC, on/off state only
GRV-IACI-12	AC input, 12 channels, 85–140 VAC, channel-to-channel isolation
GRV-IACIS-12	AC input, 12 channels, 85–140 VAC, channel-to-channel isolation, on/off state only
GRV-IACHV-24	AC input, 24 channels, 180–280 VAC
GRV-IACHVS-24	AC input, 24 channels, 180–280 VAC, on/off state only
GRV-IACIHV-12	AC input, 12 channels, 180–280 VAC, channel-to-channel isolation
GRV-IACIHVS-12	AC input, 12 channels, 180–280 VAC, channel-to-channel isolation, on/off state only
GRV-IDC-24	DC input, 24 channels, 15–30 V
GRV-IDCS-24	DC input, 24 channels, 15–30 V, on/off state only
GRV-IDCSW-12	DC input, 12 channels, switch status
GRV-IDCI-12	AC/DC discrete input, 12 channels, 10–30 VDC, 10–25 VAC, channel-to-channel isolation
GRV-IDCIS-12	DC input, 12 channels, 10–30 V, channel-to-channel isolation, on/off state only
GRV-IDCIFQ-12	DC input, 12 channels, 2.5–30 V, channel-to-channel isolation, high speed, quadrature
GRV-IACDCTL-24	AC/DC input, polarity insensitive, 24 channels, 2–16 V AC/DC
GRV-IACDCTL-24	AC/DC input, polarity insensitive, 24 channels, 2–16 V AC/DC, on/off state only

groov Discrete Output Modules

GRV-OAC-12	AC output, 12 channels, 12–250 VAC
GRV-OACS-12	AC output, 12 channels, 12–250 VAC, on/off only
GRV-OACI-12	AC output, 12 channels, 12–250 VAC, channel-to-channel isolation
GRV-OACIS-12	AC output, 12 channels, 12–250 VAC, channel-to-channel isolation, on/off only
GRV-ODCI-12	DC output, 12 channels, 5–60 VDC, channel-to-channel isolation
GRV-ODCIS-12	DC output, 12 channels, 5–60 VDC, channel-to-channel isolation, on/off only
GRV-ODCSRC-24	DC output, 24 channels, 5–60 VDC, sourcing
GRV-OMRIS-8	AC/DC output, 8 channels, mechanical relay, 0–250 VAC/5–30 VDC, 5 A

groov Mixed Signal, Multifunction Modules

GRV-MM1001-10	8 multifunction, mixed signal channels; 2 form C electromechanical relay output channels
---------------	--

groov Serial Modules

GRV-CCANI-2	Serial communication, 2 channels, CAN, channel-to-channel isolation
GRV-CSERI-4	Serial communication, 4 channels, RS-232 or RS-485, channel-to-channel isolation

groov RIO Modules

Intelligent I/O modules that can work independently as data acquisition points in Node-RED flows and custom control programs, or as remote I/O units in CODESYS applications and PAC Control strategies.

- [GRV-R7-MM1001-10](#) (*groov* RIO MM1) Remote Universal I/O; 8 software-configurable channels; 2 form C electromechanical relay output channels
- [GRV-R7-MM2001-10](#) (*groov* RIO MM2) Remote Universal I/O; 8 software-configurable channels; 2 form C electromechanical relay output channels, Ignition 8
- [GRV-R7-I1VAPM-3](#) *groov* RIO edge EMU; 3-phase power and energy monitoring, 18 data & accumulation values per phase; 10 summation values

Software

groov RIO modules come with [groov Manage](#), [Node-RED](#), and [Secure Shell](#) pre-installed. *groov* RIO MM2 also includes [Ignition Edge](#)® 8 pre-installed. Order license below for Secure Shell and Ignition Edge.

- [GROOV-LIC-EDGE8](#) *groov* EPIC/RIO license for Ignition Edge version 8
- [GROOV-LIC-SHELL](#) *groov* EPIC/RIO license for Secure Shell access

groov EPIC processors come with [groov Manage](#), [groov View](#), [PAC Control Runtime](#), and [Node-RED](#). They also come with [CODESYS](#)® Runtime, [Ignition Edge](#), and [Secure Shell](#) pre-installed; order license below:

- [GROOV-LIC-CRE](#) *groov* EPIC license for CODESYS Runtime
- [GROOV-LIC-EDGE](#) *groov* EPIC license for Ignition Edge version 7
- [GROOV-LIC-EDGE8](#) *groov* EPIC/RIO license for Ignition Edge version 8
- [GROOV-LIC-SHELL](#) *groov* EPIC/RIO license for Secure Shell access

groov EPIC & groov RIO Accessories

- [GRV-TERM26-5](#) *groov* I/O module terminal, 5 pack
- [GRV-TERMG26-5](#) *groov* I/O module terminal, gray, for thermocouple modules, 5-pack
- [GRV-TERMPM13-5](#) *groov* I/O module terminal, for power-monitoring modules, 5-pack
- [GRV-TEX-26F6](#) 26-wire cable for *groov* I/O and *groov* RIO modules. Straight-through; no common terminals. Flying leads.
- [GRV-TEX-SCTOOL](#) *groov* spring clamp terminal tool
- [GRV-TEX-RCTM-5](#) *groov* RIO cable tie push mount, 5 pack
- [GRV-ENC-POLY-SM](#) *groov* EPIC/RIO enclosure, 1–2 devices/chassis, polycarbonate, wall or panel mount, IP65
- [GRV-ENC-POLY-MD](#) *groov* EPIC/RIO enclosure, 1–4 devices/chassis, polycarbonate, wall or panel mount, IP69
- [GRV-EPIC-PSAC-FUSE-5](#) Pack of 5 2-amp 250 V slow fuses for the GRV-EPIC-PSAC power supply
- [GRV-EPIC-PSDC-FUSE-5](#) Pack of 5 4-amp 250 V slow fuses for the GRV-EPIC-PSDC power converter
- [GRV-EPIC-PSPT-FUSE-5](#) Pack of 5 10-amp 125 V fast fuses for the GRV-EPIC-PSPT power adapter

groov EPIC & groov RIO Learning Centers

- [GRV-EPIC-LC](#) *groov* EPIC Learning Center
- [GRV-RIO-LC](#) *groov* RIO Learning Center (includes GRV-R7-MM1001-10)
- [GRV-RIO2-LC](#) *groov* RIO Learning Center (includes GRV-R7-MM2001-10 module, which adds Ignition and Ignition Edge® software from Inductive Automation®)

- Web-based commissioning, troubleshooting, and *groov* View HMI display
- LCD touch display
- Dual USB ports for serial communications, touchscreen monitors, or WiFi adapters
- HDMI port for external monitors
- Dual independent Gigabit Ethernet network interfaces
- Chassis for 0, 4, 8, or 16 *groov* I/O modules (discrete, analog, serial, mixed signal multifunction)
- Control, display, and IIoT software:
 - PAC Project Basic
 - CODESYS with IEC 61131-3 languages
 - Ignition/Ignition Edge with PLC drivers
 - MQTT/Sparkplug B
 - *groov* View HMI
 - Node-RED



groov I/O module features:

- LEDs indicate module health and channel status
- Pivoting, two-position cover
- Touch-sensitive pad
- Hot swappable



Power supply available in three models:

- AC power supply
- DC power converter
- Pass-through power adapter

Chassis available in four models:

- 0-module
- 4-module (shown)
- 8-module
- 16-module

With both *groov* EPIC and *groov* RIO, you get:

- *groov* Manage
- Node-RED
- Removable terminal connector
- UL Hazardous Locations approval and ATEX compliance



- Models available for energy monitoring and for multifunction/multi-signal configuration
- Software-configurable channels
- Power over Ethernet (PoE) can supply power to module and I/O. Or connect a 10–32 VDC power supply.
- Collect and publish data:
 - MQTT/Sparkplug B
 - Node-RED
 - Ignition/Ignition Edge (MM2 model only)

