



M610 Bluetooth Handheld Label Maker with Hard Case

Part Number: M610-B-KIT

Product Highlights

Maximum Label/Tape Width: 2 in

Color Printing Capability: Single Color

Maximum Labels per Day: 750

Stand Alone Printing: PC connected & Stand-alone

Print Resolution: 300 dpi

Print Technology: Thermal Transfer

Overview

Get the durability your work demands: Bluetooth connectivity, shock resistance, below freezing operating temps and the widest range of data entry options. Includes Brady Workstation Basic Design Suite software and a hard case.

- Design and print labels using a keypad, mobile app or desktop software
- Work longer with an enhanced Gen3 Li-ION battery – print 4,500 labels on a full charge
- Stay connected wherever your work happens with enhanced Bluetooth technology
- Stay connected wherever your work happens with enhanced Bluetooth technology
- Print labels at 2" per second print speed
- Get added durability with a printer that is resistant to military-grade shocks (MIL-STD-810G) and 6-foot drops
- Operate your printer in 0°-115°F temperatures
- NOTICE: Brady North America is not authorized to ship this item via air or to Alaska or Hawaii. Please contact your local distributor.

Label creation, just a tap away.

Seamlessly design, view and print labels right from our industry-leading app.

The M610 Printer with Bluetooth, paired with Express Labels mobile app, provides a seamless on-demand experience for maximum on-site efficiency.

Specification

Key Characteristics	Product Number	175670
	UPC	888434620465
	UOM	Each
	Trade Name	M610
	Brand Name	Brady®
	Country of Origin	Malaysia
	HTS Code (Harmonized Tariff Schedule)	8443.32.1050

	ECCN (Export Commodity Control Number)	EAR99
--	--	-------

Dimensions	Dimensions	12.93 in H x 4.22 in W x 4.19 in D
	Height	12.93 in
	Width	4.22 in
	Depth	4.19 in
	Display Size	2.8 in
	Weight	3.10 lb

Material Characteristics	Color	Yellow, Gray
--------------------------	-------	--------------

Product Features	Application	Asset Tracking, Circuit Board Labeling, Data and Telecommunications Labeling, Electrical Labeling, Facility Identification, General Identification, Safety Identification, Wire and Cable Labeling
	Shipped With Battery	Yes
	How Is Battery Shipped	Shipped in box, not installed
	Battery mAh Rating	2700 mAh
	Battery Weight (metric)	0.40 lb
	Built-In Label Wizards	Flags, Patch Panel, Terminal Block, Wire Wrap
	Connectivity Options	Bluetooth
	Cutter Type	Manual cut
	Display Type	Color LCD Screen, LCD backlit graphics display
	Keyboard Type	QWERTY
	Memory	512 MB RAM, 256 MB Flash
	Stand Alone Printing	PC connected & Stand-alone

	Number of Symbols	480
	Plug Type	US
	Power Supply Voltage	110 - 240 V
	Auto Shut-Off / Power Conserve	User Configurable
	Recharge Time	4 hours
	Special Characters Quantity	123
	User Interface Type	Full QWERTY Keyboard, Mobile device, PC
	Battery Type	Rechargeable Lithium-ion Battery


Printing Specifications	Barcode Symbologies - 2D	Data Matrix, QR code
	Barcode Symbologies - Linear	Code 128, Code 39, EAN-13, EAN-8, Interleaved 2 of 5, More through Brady WorkStation, UPC-A, UPC-E
	Calibration Required?	Automated through Smart Cell
	Color Printing Capability	Single Color
	Font Sizes	4 - 170 pt
	Font Styles	Brady Alpine, Brady Fixed Width
	Label Retention Feature	Yes
	Maximum Labels per Day	750
	Minimum Label Length	0.236 in
	Maximum Print Speed	2.0 in/s
	Minimum Liner Width	0.812 in
	Print Resolution	300 dpi
	Print Technology	Thermal Transfer
	On Screen Indicators	Battery Life, Bluetooth Status, Ribbon and label part number recognition, Ribbon Remaining, Supply Remaining

	Device Drop Test & Durability	Resistant to 4-foot drops, Resistant to military-grade shocks (MIL-STD-810G)
--	-------------------------------	---

Compatibility	Compatible Media	BM-, BMC-, M6-, M6C-
	Label Material Types	FreezerBondz™ Polyester, Heat-shrink Polyolefin, High Temperature Heat-shrink Polyvinylidene Fluoride Sleeve, Metallized Polyester, Metallized Polyester with Polyester Overlamine, Nylon Cloth, Paper, Polyester, Polyethylene, Polyethylene Foam Laminate Polyester, Polyimide, Polyolefin, Polypropylene, Polyvinylfluoride, Reflective Tape, Self-laminating Polyester, Self-laminating Vinyl, StainerBondz™ Polyester, Static Dissipative Polyester, Tamper-evident Metallized Polyester, Tamper-evident Polyester, Tamper-resistant Metallized Vinyl, Tamper-resistant Vinyl, Vinyl, Vinyl Cloth
	Continuous & Die-Cut Materials Supported	Continuous and Die-cut
	Custom Labels Available	Yes
	Maximum Label/Tape Width	2 in
	Maximum Print Width	2 in
	Maximum Printed Label Length	40 in
	Maximum Liner Width	2.25 in
	Phones & Tablets Supported	Android devices with Android OS 5+, iPhone 5S or newer with iOS 10+
	Software Compatibility	Brady Workstation, Express Labels Mobile App

	Languages Available	Bulgarian, Croatian, Czech, Danish, Dutch, English (US), Estonian, Finnish, French (France), German, Hungarian, Italian, Norwegian, Polish, Portuguese (Portugal), Romanian, Russian, Slovak, Slovenian, Spanish (Spain), Swedish, Turkish
--	---------------------	--

What's Included	Includes	(1) AC Adapter/Battery Charger (M-AC-POWER), (1) Black Ribbon (M61-R4310), (1) Brady WorkStation Basic Design Software, (1) Hard Case (M610-HC), (1) Li-ION Rechargeable Battery (M-LION-BATTERY), (1) M610 Label Printer w Bluetooth, (1) Printed Quick Start Guide, (1) Product USB, (1) Self Laminating Cable Wraps (M6-11-427), (1) USB Cord
	Warranty (North America)	2 Years

Compliance	UNSPSC	45101520
	California Prop 65	 WARNING: Cancer and Reproductive Harm - www.p65warnings.ca.gov
	RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863