



M610 Handheld Label Maker with Hard Case

Part Number: M610-KIT

Product Highlights

Maximum Label/Tape Width: 2 in

Color Printing Capability: Single Color

Maximum Labels per Day: 750

Stand Alone Printing: PC connected & Stand-alone

Print Resolution: 300 dpi

Print Technology: Thermal Transfer

Overview

Get the durability your work demands: military-grade shock resistance, below freezing operating temps and the widest range of data entry options. Kit includes a hard case.

- Design and print labels using a keypad or desktop software
- Work longer with an enhanced Gen3 Li-ION battery – print 4,500 labels on a full charge
- Easily import and export label files, lists and graphics to the printer through USB 2.0 port (Type A and B) or USB flash drive
- Print labels at 2" per second print speed
- Get added durability with a printer that is resistant to military-grade shocks (MIL-STD-810G) and 6-foot drops
- Operate your printer in 0°-115°F temperatures
- NOTICE: Brady North America is not authorized to ship this item via air or to Alaska or Hawaii. Please contact your local distributor.

The BMP®61 Label Printer has been updated to the M610 — see what's improved:

- Faster print speeds, enabling printing up to 2 inches per second
- Upgraded from NiMH to Li-ION battery pack — lighter and faster — same as on AC
- Now print barcode fonts >10pt, 2D barcodes, ISO 7010 symbols and store files on printer
- Added durability to withstand up to 6 foot drop and meets MIL-STD-810G vibration testing

Key Characteristics	Product Number	175669
	UPC	888434620458
	UOM	Each
	Trade Name	M610
	Brand Name	Brady®
	Country of Origin	Malaysia
	HTS Code (Harmonized Tariff Schedule)	8443.32.1050

	ECCN (Export Commodity Control Number)	EAR99
--	--	-------

Dimensions	Dimensions	12.93 in H x 4.22 in W x 4.19 in D
	Height	12.93 in
	Width	4.22 in
	Depth	4.19 in
	Display Size	2.8 in
	Weight	3.10 lb

Material Characteristics	Color	Yellow, Gray
--------------------------	-------	--------------

Product Features	Application	Asset Tracking, Circuit Board Labeling, Data and Telecommunications Labeling, Electrical Labeling, Facility Identification, General Identification, Safety Identification, Wire and Cable Labeling
	Shipped With Battery	Yes
	How Is Battery Shipped	Shipped in box, not installed
	Battery mAh Rating	2700 mAh
	Battery Weight (metric)	0.40 lb
	Built-In Label Wizards	Flags, Patch Panel, Terminal Block, Wire Wrap
	Connectivity Options	Standalone Use, USB 2.0
	Cutter Type	Manual cut
	Display Type	Color LCD Screen, LCD backlit graphics display
	Keyboard Type	QWERTY
	Memory	512 MB RAM, 256 MB Flash
	Stand Alone Printing	PC connected & Stand-alone

	Number of Symbols	480
	Plug Type	US
	Power Supply Voltage	110 - 240 V
	Auto Shut-Off / Power Conserve	User Configurable
	Recharge Time	4 hours
	Special Characters Quantity	123
	User Interface Type	Full QWERTY Keyboard, PC
	Battery Type	Rechargeable Lithium-ion Battery


Printing Specifications	Barcode Symbologies - 2D	Data Matrix, QR code
	Barcode Symbologies - Linear	Code 128, Code 39, EAN-13, EAN-8, Interleaved 2 of 5, More through Brady WorkStation, UPC-A, UPC-E
	Calibration Required?	Automated through Smart Cell
	Color Printing Capability	Single Color
	Font Sizes	4 - 170 pt
	Font Styles	Brady Alpine, Brady Fixed Width
	Label Retention Feature	Yes
	Maximum Labels per Day	750
	Maximum Print Speed	2.0 in/s
	Minimum Label Length	0.236 in
	Print Resolution	300 dpi
	Minimum Liner Width	0.812 in
	Print Technology	Thermal Transfer
	On Screen Indicators	Battery Life, Ribbon and label part number recognition, Ribbon Remaining, Supply Remaining

	Device Drop Test & Durability	Resistant to 4-foot drops, Resistant to military-grade shocks (MIL-STD-810G)
--	-------------------------------	--

Compatibility	Compatible Media	BM-, BMC-, M6-, M6C-
	Label Material Types	FreezerBondz™ Polyester, Heat-shrink Polyolefin, High Temperature Heat-shrink Polyvinylidene Fluoride Sleeve, Metallized Polyester, Metallized Polyester with Polyester Overlaminate, Nylon Cloth, Paper, Polyester, Polyethylene, Polyethylene Foam Laminate Polyester, Polyimide, Polyolefin, Polypropylene, Polyvinylfluoride, Reflective Tape, Self-laminating Polyester, Self-laminating Vinyl, StainerBondz™ Polyester, Static Dissipative Polyester, Tamper-evident Metallized Polyester, Tamper-evident Polyester, Tamper-resistant Metallized Vinyl, Tamper-resistant Vinyl, Vinyl, Vinyl Cloth
	Continuous & Die-Cut Materials Supported	Continuous and Die-cut
	Custom Labels Available	Yes
	Maximum Label/Tape Width	2 in
	Maximum Print Width	2 in
	Maximum Printed Label Length	40 in
	Maximum Liner Width	2.25 in
	Phones & Tablets Supported	Android devices with Android OS 5+, iPhone 5S or newer with iOS 10+
	Software Compatibility	Brady Workstation

	Languages Available	Bulgarian, Croatian, Czech, Danish, Dutch, English (US), Estonian, Finnish, French (France), German, Hungarian, Italian, Norwegian, Polish, Portuguese (Portugal), Romanian, Russian, Slovak, Slovenian, Spanish (Spain), Swedish, Turkish
--	---------------------	--

What's Included	Includes	(1) AC Adapter/Battery Charger (M-AC-POWER), (1) Black Ribbon (M61-R4310), (1) Brady WorkStation Basic Design Software, (1) Hard Case (M610-HC), (1) Li-ION Rechargeable Battery (M-LION-BATTERY), (1) M610 Label Printer (M610), (1) Printed Quick Start Guide, (1) Product USB, (1) Self Laminating Cable Wraps (M6-11-427), (1) USB Cord
	Warranty (North America)	2 Years

Compliance	UNSPSC	45101520
	California Prop 65	 WARNING: Cancer and Reproductive Harm - www.p65warnings.ca.gov
	RoHS Compliance Status	Compliant with Directive 2011/65/EU and 2015/863