

## RefLED Superia Retro MR16

RefLED Superia Retro MR16 V2 600LM 830 36° SL

0029233



### Product features

- Compact, energy efficient and exceptional value for money product Same shape and size as halogen MR16 lamp Compact Cluster SMD technology enabling high efficiency with halogen look Reduced visible heat sink from the front Available in 36 degree High lumen efficacy 12V AC/DC 25,000 hours average rated life 5 years warranty



## PRODUCT OVERVIEW

Product name	RefLED Superia Retro MR16 V2 600LM 830 36° SL
Technology	LED
Watt (Rated) (W)	6
Type	LED exchangeable
Cap/Base	GU5.3
Fixture rating	Open
General application	Education, Hospitality, Residential & Consumer
ETIM Class	EC001959
E-number FI	4741113
Warranty	3 years
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Colour Consistency (SDCM)	6
Beam Angle (°)	36
Photobiological Risk Group	RG1
Wattage (W)	6
Product Voltage (V)	12
Dimmable	No
Average life (Nominal) (h)	25000
Product EAN number	5410288292335

## DATA TABLE

### General data

Product name	RefLED Superia Retro MR16 V2 600LM 830 36° SL
Technology	LED
Watt (Rated) (W)	6
Type	LED exchangeable
Cap/Base	GU5.3
Fixture rating	Open
General application	Education, Hospitality, Residential & Consumer
Operating temperature range (°C)	-20°C - 40°C

## RefLED Superia Retro MR16

*RefLED Superia Retro MR16 V2 600LM 830 36° SL*

0029233

Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4741113
Warranty	3 years

### Optical data

Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Colour Consistency (SDCM)	6
Luminous Intensity (cd)	1000
Beam Angle (°)	36
Photobiological Risk Group	RG1
Lumen maintenance at end of nominal life (%)	70

### Electrical data

Wattage (W)	6
Equivalent watt (W)	49
Product Voltage (V)	12
Control gear required	No
No. Of switching cycles before premature failures	>50000
Transformer required	Yes
Dimmable	No
Lamp Energy Label (class)	F

### Lifetime data

Lifespan L70 B50	25000
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000

### Physical data

Nominal Product Length (mm)	44
Nominal Product Diameter (mm)	50
Weight (kg)	0.035

### Packaging

Single packaging type	Carton
Product EAN number	5410288292335
Packaging single length / height (cm)	8.2
Packaging single width (cm)	6.1
Packaging single depth (cm)	5.1
DUN14 (inner)	25410288292339
Units per inner package	6
Packaging inner length / height (cm)	9.5
Packaging inner width (cm)	17.0
Packaging inner depth (cm)	13.5

## RefLED Superia Retro MR16

*RefLED Superia Retro MR16 V2 600LM 830 36° SL*


0029233

DUN14 (outer)	15410288292332
Units per outer package	36
Packaging outer length / height (cm)	20.0
Packaging outer width (cm)	41.5
Packaging outer depth (cm)	18.0


### Safety data

Optimal operating condition (°C)	-20-40
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Not Suitable for totally enclosed fixtures

## PHOTOMETRY



## TECHNICAL DRAWINGS



## RefLED Superia Retro MR16


*RefLED Superia Retro MR16 V2 600LM 830 36° SL*

0029233



**SYLVANIA**

0029233



**6**  
kWh/1000h



2019/2015

## RefLED Superia Retro MR16


*RefLED Superia Retro MR16 V2 600LM 830 36° SL*

0029233



SYLVANIA

0029233



**6**  
kWh/1000h



2019/2015