

BR500 High Definition Articulating Videoscope

2-way articulating probe adjusts 135° in both directions

Features:

- 4 adjustable LEDs can illuminate totally darkened areas for inspection
- 3.5" Color TFT LCD monitor with 320 x 240 resolution
- 6mm camera head is waterproof (IP67)
- Built-in clock/calendar
- Record video (.ASF) and images (.JPG)
- SWR (Snapshot while recording) function during video recording or playback
- View captured video/images on the display or transfer to your PC using the USB interface or removable SD card (16GB max)
- Store up to 150k images on the included 8GB SD card
- Audio/Video output for connection to a monitor (NTSC or PAL format)
- Auto power off with disable
- Complete with Videoscope, handset with articulating probe, 3.7V rechargeable battery, cleaning kit, 100-240V AC adapter/charger with 4 connectors (US, UK, EU, AUS), SD card, USB and AV cables and heavy duty carrying case



Specifications

Camera	
Diameter	6mm
Field of View	60°
Depth of View	0.8~2.4" (20~60mm)
Resolution	640 x 480 pixels
Articulation	270° (135° left, 135° right)
Display Unit	
Display	3.5" Color TFT (320 x 240 pixels)
Interface	mini USB/AV output
Video Output Format	NTSC or PAL
Storage	8G SD Card included (up to 16GB max)
Still Image Format	JPEG (640 x 480)
Video Recording Format	ASF (640 x 480)
Power	3.7V Li-Po Battery or AC Adapter
Dimensions (Main Unit)	8.5 x 4.5 x 1.5" (216 x 114 x 38.1mm)
Weight	0.9lbs (0.4kg)
Dimensions (Articulating Probe)	Handle: 1' x 2.1" (3.4.8 x 53.3mm)/Cable: 3.3ft (1m)
Weight	1lbs (0.5kg)

Applications:

Inspect cable connections on the back of installed equipment; Plumbing and Electrical installations behind walls and hard-to-reach areas; HVAC and Heating duct work or in and around the heat exchanger, "A Coil" and evaporator; Automotive sensors and engine parts; Insect or rodent infestation; Anywhere you need to see underneath and behind difficult to move objects

Ordering Information:

BR500 High Definition Articulating Videoscope

