

1394132-1 ✓ ACTIVE

TE Internal #: 1394132-1


Automotive Seals & Cavity Plugs, Cavity Blanking Plug, Cavity

Diameter .142 in [3.6 mm], Silicone, Poor, 50, Natural

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Seals & Cavity Plugs



Connector Seal Type: **Cavity Blanking Plug**

Cavity Diameter: **3.6 mm [.142 in]**

Seal Material: **Silicone**

Resistance to Hydrocarbons: **Poor**

Shore A Hardness: **50**

Features

Product Type Features

Connector Seal Type	Cavity Blanking Plug
---------------------	----------------------

Body Features

Seal Material	Silicone
---------------	----------

Primary Product Color	Natural
-----------------------	---------

Dimensions

Cavity Diameter	3.6 mm [.142 in]
-----------------	------------------

Usage Conditions

Operating Temperature (Max)	130 °C [266 °F]
-----------------------------	-----------------

Industry Standards

UL Flammability Rating	None
------------------------	------

Other

Resistance to Hydrocarbons	Poor
----------------------------	------

Shore A Hardness	50
------------------	----

Contains Lubricant	No
--------------------	----



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer





This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 953756-3 PC 47V RIGHT BLACK</p>	 <p>TE Part # 2299987-1 65W PLUG ASSEMBLY</p>	 <p>TE Part # 2299987-3 65W PLUG ASSEMBLY</p>	 <p>TE Part # 2299987-4 65W PLUG ASSEMBLY</p>
--	--	--	--



Customers Also Bought



Documents

Product Drawings

[BLINDSTOPFEN F.D3,6](#)

German

CAD Files

[3D PDF](#)

3D

[Customer View Model](#)

[ENG_CVM_CVM_1394132-1_A.2d_dxf.zip](#)



English

Customer View Model

[ENG_CVM_CVM_1394132-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1394132-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[HDSCS CAN Bus Y-Connector and 120 Resistor Brochure](#)

English

[HDSCS Catalog](#)

English

[CONNECTOR SELECTOR](#)

English

Product Specifications

[Application Specification](#)

French

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

French