

CATALOG NUMBER

DT115030R



FEATURES

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- External back-up fuse is not required up to 315 A (IEC only)
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

PRODUCT ATTRIBUTES

- Nominal System Voltage (Un): 120 V
- Max Continuous Operating Voltage (Uc): 150 V
- Nominal Discharge Current (In), IEC: 20 kA 8/20 μ s
- Max Discharge Current (Imax), IEC: 50 kA 8/20 μ s
- Impulse Current (Iimp): 12.50 kA 10/350 μ s
- Voltage Protection Level (Up): 1,000 V
- Response Time: 25 ns Max
- Back-Up Fuse @ Isccr: 250 A @ 50 kA; 315 A @ 25 kA
- Frequency: 50 – 60 Hz
- Short Circuit Current Rating (Isccr): 25 kA; 50 kA
- Protection Modes: L-PEN
- Temporary Over Voltage 120 min (Ut/mode): 229 V Safe Fail
- Temporary Over Voltage Withstand 5 s (Ut): 175 V
- Voltage Protection Rating (VPR): 700 V

Nominal Discharge Current (In), UL: 20 kA 8/20 μ s

Replacement Module: DT1150M

Short Circuit Current Rating (SCCR): 200 kA

Technology: Thermal Disconnect

Connection, Solid: #2 Max

Connection, Stranded: #4 Max

Torque: 3.32 ft lb

Humidity: 5 – 95 % RH

Temperature: -31 to 185 °F

Enclosure Material: UL® 94V-0 Thermoplastic

Enclosure Rating: IP 20

Mounting: 35 mm top hat DIN rail

Remote Contact Switching Capacity: 0.5 A @ 12 VDC; 0.5 A @ 24 VDC; 0.5 A @ 48 VDC; 1.0 A @ 125 VAC; 1.0 A @ 250 VAC

Remote Contacts: Yes

Status Indication: Mechanical flag

Depth: 3.350"

Height: 3.540"


Width: 2.130"

Unit Weight: 1.041 lb

Certification Details: UL® 1449 Edition 5 Type 1CA

Complies With: EN 61643-11 Type 1, Type 2; IEC® 61643-11 Class I, Class II

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER