

## CATALOG NUMBER

**UTB110SP**



## CERTIFICATIONS



## FEATURES

Compact design universal transient barrier provides protection of low-voltage circuits and transducers

Separate plug and base design allows hot swappable module replacement

Multi-stage protection and fine over-voltage protection helps ensure lowest residual surge voltages reach sensitive equipment

Common-mode and differential-mode protection protects against both possible surge conditions

Surge rating to 20 kA 8/20  $\mu$ s is ideal for exposed wiring

Allows for protection of 25 analog signals or 50 digital signals per linear foot (0,3 m) of DIN rail space

## PRODUCT ATTRIBUTES

Nominal System Voltage ( $U_n$ ): 100 - 120 VAC;60 - 154 VDC

Max Continuous Operating Voltage ( $U_c$ ): 150 VAC;170 VDC

Rated Load Current ( $I_L$ ): 2 A

Frequency: 3 MHz

Loop Resistance: 1  $\Omega$

Max Discharge Current ( $I_{max}$ ), L+L-PE: 20 kA 8/20  $\mu$ s

Protection Modes: Common;Differential

Technology: Gas Discharge Tube (GDT);Metal Oxide Varistor (MOV);Silicon Avalanche Diode (SAD)

Voltage Protection Level (Up), L-L: 220 V @ 3 kA

Connection, Stranded: #18 – #12

Mounting: 35 mm top hat DIN rail

Temperature: -4 to 149 °F

Enclosure Material: UL® 94V-0 Thermoplastic

Enclosure Rating: IP 20;NEMA®-1

Depth (D): 2.830"

Height (H): 3.540"

Width (W): 0.470"


Unit Weight: 0.150 lb

Certification Details: UL® 497B

Complies With: ANSI®/IEEE® C62.41.2-2002 Cat A, Cat B, Cat C

Replacement Module: UTB110SPM

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

**Europe**

Netherlands:

+31 800-0200135

France:

+33 800 901 793

**Europe**

Germany:

800 1890272

Other Countries:

+31 13 5835404

**APAC**

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**