



Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Caps & Covers



Protection & Strain Relief Accessory Type: **Cover**

Cable Exit Angle: **180°**

Primary Product Color: **Black**

Primary Product Material: **PBT**

Operating Temperature (Max): **125 °C [257 °F]**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Cover
Sealable	No

Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Primary Product Material	PBT

Dimensions

Compatible Cable Bundle Diameter Range	4 mm[.157 in]
--	---------------

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------



Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 9-2348772-1
HD MATEnet 3+0 TAB HSG ASSY, GRP E



TE Part # 9-2348772-2
HD MATEnet 3+0 TAB HSG ASSY, GRP E



TE Part # 9-2348776-1
HD MATEnet 3+0 REC HSG ASSY, GRP E



TE Part # 9-2348776-2
HD MATEnet 3+0 REC HSG ASSY, GRP E





TE Part # 9-2348782-1
HD MATEnet 2+6 TAB HSG ASSY, GRP E



TE Part # 9-2348782-2
HD MATEnet 2+6 TAB HSG ASSY, GRP E



TE Part # 9-2348786-1
HD MATEnet 2+6 REC HSG ASSY, GRP E



TE Part # 9-2348786-2
HD MATEnet 2+6 REC HSG ASSY, GRP E



TE Part # 9-2348789-1
HD MATEnet 2+6 TAB ASSY, GRP E, FLANGED



TE Part # 9-2348789-2
HD MATEnet 2+6 TAB ASSY, GRP E, FLANGED



TE Part # 9-2348792-1
HD MATEnet 1+12 TAB HSG ASSY, GRP E



TE Part # 9-2348792-2
HD MATEnet 1+12 TAB HSG ASSY, GRP E



TE Part # 9-2348795-1
HD MATEnet 1+12 REC HSG ASSY, GRP E




TE Part # 9-2348795-2
HD MATEnet 1+12 REC HSG ASSY, GRP E

TE Part # 9-2354265-1
HD MATEnet 1+2 REC HSG CAV BLOCK, GRP C

TE Part # 9-2354265-2
HD MATEnet 1+2 REC HSG CAV BLOCK, GRP C

TE Part # 9-2348798-1
HD MATEnet 1+12 TAB ASSY, GRP E, FLANGED

Also in the Series | Heavy Duty Sealed Connector Series




Automotive Connector Caps & Covers (25)



Automotive Housings(207)



Automotive Seals & Cavity Plugs(5)




Data Connectivity Headers(2)



Data Connectivity Housings(18)



Other Automotive Connector Accessories(34)



PCB Headers & Receptacles(1)

Also in the Series | **MATEnet**



Automotive Connector Caps & Covers (5)



Automotive Housings(1)



Automotive Seals & Cavity Plugs(5)



Data Connectivity Headers(7)



Data Connectivity Housings(31)



Other Automotive Connector Accessories(1)



PCB Headers & Receptacles(2)

Customers Also Bought



TE Part #HD10-5-16P-B009
SQ FG REC ASM



TE Part #DRC12-24PC
REC, 24P, BLK, N, FLANGE, C



TE Part #DTM06-12SD-EE04
PLG, 12P, BLK, N, HIGH TEMP, D



TE Part #HDP26-18-20SN-L017
PLG, 20P, BLK, N, RNG, 16/20, S



TE Part #DT06-12SD-C015
PLG, 12P, BRN, E, D




TE Part #2304168-2
4POS MATE-AX, HDR ASSY,90 DEG, COD B



TE Part #2348770-3
HD MATEnet - COVER FOR SWS



TE Part #DTCE02-1-4P-E003
DTCE RECP ASM



Documents

Product Drawings

HD MATEnet - COVER FOR SWS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2348770-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2348770-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2348770-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English