

## DT2 DIN RAIL SURGE PROTECTION CLASS II, 1+0 MODE, 120 V UN

### CATALOG NUMBER

**DT215010R**



### CERTIFICATIONS



### FEATURES

Compact, yet high surge rated pluggable design, using minimum DIN rail width

External back-up fuse is not required up to 315 A (IEC only)

Retaining clip ensures enhanced vibration and shock resistance performance

Red/Green status indication and change-over contacts standard for remote monitoring

### PRODUCT ATTRIBUTES

Nominal System Voltage (Un): 120 V

Max Continuous Operating Voltage (Uc): 150 V

Nominal Discharge Current (In), IEC: 20 kA 8/20  $\mu$ s

Max Discharge Current (Imax), IEC: 50 kA 8/20  $\mu$ s

Voltage Protection Level (Up): 1,250 V

Back-Up Fuse @ Isccr: 250 A @ 50 kA; 315 A @ 25 kA

Frequency: 50 – 60 Hz

Response Time: 25 ns Max

Protection Modes: L-PE;N-PE;L-N;L-PEN

Short Circuit Current Rating (Isc cr): 25 kA;50 kA

Temporary Over Voltage 120 min (Ut/mode): 229 V Safe Fail

Temporary Over Voltage Withstand 5 s (Ut): 229 V

Nominal Discharge Current (In), UL: 20 kA 8/20  $\mu$ s

Short Circuit Current Rating (SCCR): 200 kA

Voltage Protection Rating (VPR): 700 V

Technology: Thermal Disconnect

Connection, Solid: #2 Max

Connection, Stranded: #4 Max

Torque: 3.32 ft lb

Humidity: 5 – 95 % RH

Temperature: -31 to 185 °F

Enclosure Material: UL® 94V-0 Thermoplastic

Enclosure Rating: IP 20

Mounting: 35 mm top hat DIN rail

Remote Contact Switching Capacity: 1.0 A @ 250 VAC;1.0 A @ 125 VAC;0.5 A @ 48 VDC;0.5 A @ 24 VDC;0.5 A @ 12 VDC

Remote Contacts: Yes

Status Indication: Mechanical flag

Depth: 2.720"

Height: 3.540"

Width: 0.710"


Unit Weight: 0.283 lb

Certification Details: UL® 1449 Edition 5 Type 1CA

Complies With: EN 61643-11 Type 2;IEC® 61643-11 Class II

Replacement Module: DT2150M

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**