

## DT2 DIN RAIL SURGE PROTECTION CLASS II, 2+0 MODE, 120 V UN

### CATALOG NUMBER

**DT215020R**



### FEATURES

- Compact, yet high surge rated pluggable design, using minimum DIN rail width
- External back-up fuse is not required up to 315 A (IEC only)
- Retaining clip ensures enhanced vibration and shock resistance performance
- Red/Green status indication and change-over contacts standard for remote monitoring

### PRODUCT ATTRIBUTES

- Nominal System Voltage (Un): 120 V
- Max Continuous Operating Voltage (Uc): 150 V
- Nominal Discharge Current (In), IEC: 20 kA 8/20  $\mu$ s
- Max Discharge Current (Imax), IEC: 50 kA 8/20  $\mu$ s
- Voltage Protection Level (Up): 1,250 V
- Back-Up Fuse @ Isccr: 250 A @ 50 kA; 315 A @ 25 kA
- Frequency: 50 – 60 Hz
- Response Time: 25 ns Max
- Protection Modes: L-N; N-PE
- Short Circuit Current Rating (Isccr): 25 kA; 50 kA
- Temporary Over Voltage 120 min (Ut/mode): 229 V Withstand
- Temporary Over Voltage Withstand 5 s (Ut): 229 V
- Nominal Discharge Current (In), UL: 20 kA 8/20  $\mu$ s
- Short Circuit Current Rating (SCCR): 200 kA

Voltage Protection Rating (VPR): 700 V

Technology: Thermal Disconnect

Connection, Solid: #2 Max

Connection, Stranded: #4 Max

Torque: 3.32 ft lb

Humidity: 5 – 95 % RH

Temperature: -31 to 185 °F

Enclosure Material: UL® 94V-0 Thermoplastic

Enclosure Rating: IP 20

Mounting: 35 mm top hat DIN rail

Remote Contact Switching Capacity: 1.0 A @ 250 VAC;1.0 A @ 125 VAC;0.5 A @ 48 VDC;0.5 A @ 24 VDC;0.5 A @ 12 VDC

Remote Contacts: Yes

Status Indication: Mechanical flag

Depth: 2.720"

Height: 3.540"

Width: 1.420"


Unit Weight: 0.556 lb

Certification Details: UL® 1449 Edition 5 Type 1CA

Complies With: EN 61643-11 Type 2;IEC® 61643-11 Class II

Replacement Module: DT2150M

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**