



NL4FXX-W-L

4 pole speakON cable connector, screw terminal assembly,
chuck type strain relief for cable diameters 10 to 16 mm

speakON connectors are the industry-standard for loudspeaker connections. This product series offers extremely reliable and robust cable connectors with a proven twist lock system. speakON cable connectors feature solid contacts with screw-type terminals including a stranded wire protection.



Features & Benefits

- | | |
|---|---|
| <ul style="list-style-type: none">• Up to 37 A rms current rating | <ul style="list-style-type: none">• Unique Neutrik locking bushing and strain relief for cable diameters 10 mm to 16 mm |
| <ul style="list-style-type: none">• IEC 61984, UL 1977 and CSA C22.2 No.182.3 certified | <ul style="list-style-type: none">• Superior NEUTRIK quality standard, extremely robust and reliable |
| <ul style="list-style-type: none">• Easy to assemble because the strain relief locks with the insert mechanically and aligns with the housing | <ul style="list-style-type: none">• Easy and reliable twist lock system |
| <ul style="list-style-type: none">• Ergonomic design with slip-proof two-component molded housing | <ul style="list-style-type: none">• Improved kink protection by two-component bushing |

Technical Information

Product	
Title	NL4FXX-W-L
Connector series	speakON 4 pole

Electrical	
Contact resistance	$\leq 2 \text{ m}\Omega$
Dielectric strength	2.8 kVac
Insulation resistance	$> 10 \text{ G}\Omega$ (initially)
Number of electrical contacts	4
Rating Europe	IEC 61984: 37 A 250 V AC
Rating USA	UL1977: 35 A 250 V AC
Rating Canada	CSA C22.2 No.182.3: 24 A 250 V AC
Attention	<p>This product is strictly not intended for use as an AC or DC power supply connector!</p> <p>CAUTION: NOT FOR INTERRUPTING CURRENT</p>

Mechanical	
Cable O.D.	10 - 16 mm
Lifetime	typically 5'000 mating cycles
Wiresize (mm ²)	1.5 – 4 mm ²
Wiresize (AWG)	17 – 11 AWG
Locking device	Twist lock
Termination	screw type terminals

Material	
Contact plating	Ag
Contacts	Copper Alloy
Insert	Polyamide (PA6.6)
Locking element	Zinc diecast
Shell	Polyamide (PA6) / TPE
Strain relief	Polyketone
Bushing	Polypropylene / TPE

Environmental	
Temperature range	-33 °C to +80 °C
Protection class	IP20
Flammability acc. to UL94	V-0