



Application Tooling > Hand Crimping Tools



Tool Grade: **Commercial Crimp Tooling**
Ratchet Configuration: **Operator Releasable & Adjustable**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **TE Product Specification (114-)**
TE Certification: **Cannot be Certified**

Features

Other

Crimp Form-Wire Barrel Type	Open Barrel - F Crimp
Tool Grade	Commercial Crimp Tooling
Ratchet Configuration	Operator Releasable & Adjustable
Die Sets Type	Removable/Interchangeable
Specification Type	TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Manual
Tooling Type	SDE Crimp Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability




Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # 770250-1 UMNL II PIN PTPBR LP 20-14	 TE Part # 770251-3 UMNL II SOK PTPPHBZ LP 20-14	 TE Part # 350550-1 UMNL SOK 20-14 PTPBR L/P	 TE Part # 350547-1 UMNL PIN 20-14 PTPBR L/P
 TE Part # 770008-3 UMNL II SOK PTPPHBZ	 TE Part # 770007-1 UMNL II PIN PTPBR	 TE Part # 350218-1 UMNL PIN 20-14 .0126PTPBR	 TE Part # 770251-4 UMNL II SOK SN/AUNI/PHBZ LP
 TE Part # 350536-1 UMNL SOK 20-14 .0126 PTPBR	 TE Part # 2378745-2 SDE F UMNL/MNL 14-20AWG DIE SET	 TE Part # 2362810-1 SDE CRIMP HAND TOOL FRAME W /O DIES	


Customers Also Bought



TE Part #1-353080-2
DYNAMIC D-5200 HDR V ASSY 2P



TE Part #641964-1
02P UMNL PIN HDR ASSY POL 94VO



TE Part #234171-1
HHHT DYNAMIC D-5 M 12-10 ASSY

Documents

Datasheets & Catalog Pages

CRIMPING TERMINALS

English

Bottoming Dies

English

SDE Crimp Commercial Tool System

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English