Emergency Stop Switch multicomp PRO

Specifications

Mechanical life : >0.3 million operations Electrical life : >0.1 million operations

: 1,000,000 cycles AC-15, 230V/2A Electrical durability 1,000,000 cycles DC-13, 24V/1.5A

Rate insulation voltage Rated thermal current : 10A

Lamp socket (load) : 40V AC max. 5W max. Contact resistance : 100 mΩ max. (at 1A 6-8V DC) : 100 M Ω min. (at 500V DC) Insulation resistance Dielectric strength : 2,500V AC 50/60 Hz for 1 min

: Panel Front - IP66, Type 1, 4, 4X indoor & 13 Degree of protection

Terminals - IP30 (under panel)

Storage temperature : -40°C to 85°C

Operating temperature : -25°C to 70°C (with no icing and condensation) : UL508(CSA C22.2 No.14), UL1059, EN 60947-5-1, Approved standards


EN 60947-5-5, GB/T 14048.5

Operating humidity : 45% to 85% RH

Wire diameter : 14 AWG to 20 AWG, 2mm2 to 0.5mm2

Stripping length

Diagram



Contact Ratings

Raited insulation voltage (Ui)		600V					
Raited terminal current (Ith)		10A					
AC 50/60 Hz	Rate Operation Voltage (Ue)	12V	24V	120V	240V	380V	
	Resistive load AC-12 (le)	10A	10A	10A	6A	3.8A	
	Inductive load AC-15 (le)	10A	10A	6A	3A	1.9V	
DC	Rate Operation Voltage (Ue)	12V	24V	125V	250V	400V	
	Resistive load DC-12 (le)	10A	10A	2.2A	1.1A	0.7A	
	Inductive load DC-13 (le)	10A	5.8A	1.1A	0.55A	0.35A	

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro


Dimensions: Millimetres


Emergency Stop Switch multicomp PRO



Contact Block Mounting Position

	Operation				
Configuration	Mounting	Position	Free	e Push	
	1	NC •		-	
02	2	Р	-	-	
	3	NC	•	-	







Part Number Table

Description	Part Number	
Emergency Stop Switch, 2NC, Push Lock/Rotation Release, LED 24V AC-DC, Red	MP-AP2E-LTE02Q4R	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

