

902 to 928 MHz RFID Flat Panel Antenna, RHCP, 12 dBi, White ABS, N Female, IP54

LCANFP1034



Features

- · High Performance Multi-tag read/write Capabilities
- · Concealable Design
- · Right Hand Circular Polarized

Applications

- · Radio Frequency Identification
- · Inventory Management
- Access Control

- · 902 to 928 MHz Frequency Range
- · Type N Female Connector
- IP54 Rated
- · Data Collection
- Asset Tracking
- · Livestock Management

Description

L-Com's LCANFP1034 is a RHCP RFID flat panel antenna. The LCANFP1034 with a 12 dBi gain nominal is a Directional antenna. Our 902 to 928 MHz antenna has N Female connector and is IP54 Rated.

With an impedance of 50 Ohms and max input power of 50 Watts, the LCANFP1034 flat panel RHCP antenna is well suited for Radio Frequency Identification tag reading applications. This 902-928 MHz 12 dBi gain RFID antenna is highly directional providing the reader radio the capabilities of simultaneously reading a multitude of RFID tags with a high degree of accuracy.

L-Com's RFID LCANFP1034 has a radome made of ABS in White color. This N Female connectized Antenna has an overall length of 17.5 in, width of 17.5 in, and weighs 0.85 lbs. Use our on-line ordering system to purchase your LCANFP1034 RFID Directional RHCP antenna 24 hours a day with same-day shipping and no MOQs (minimum order quantities).

Configuration

Design
Application Band
Band Type
Radiation Pattern
Polarization
Connector Type
Lightning Protection

Flat Panel RFID Single Directional RHCP N Female Direct Ground

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|---------------------------|---------|---------|---------|---------|
| Frequency Range | 902 | | 928 | MHz |
| Input VSWR | | | 1.3:1 | |
| Impedance | | 50 | | Ohms |
| Gain | | 12 | | dBi |
| Horizontal (Azimuth) HPBW | | 40 | | Degrees |
| Vertical (Elevation) HPBW | | 40 | | Degrees |
| Input Power | | | 50 | Watts |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 902 to 928 MHz RFID Flat Panel Antenna, RHCP, 12 dBi, White ABS, N Female, IP54 LCANFP1034



902 to 928 MHz RFID Flat Panel Antenna, RHCP, 12 dBi, White ABS, N Female, IP54

LCANFP1034



| Axial Ratio | 3 | dB |
|-------------|---|----|
| | | |

Mechanical Specifications

Radome Material ABS

Size

 Length
 17.5 in [444.5 mm]

 Width
 17.5 in [444.5 mm]

 Height
 1.5 in [38.1 mm]

 Weight
 4.4 lbs [2 kg]

Environmental Specifications

Temperature

Operating Range -40 to +55 deg C

Ingress Protection IP54

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

902 to 928 MHz RFID Flat Panel Antenna, RHCP, 12 dBi, White ABS, N Female, IP54 from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

