

KPBA-2006SURKSYKC

2.0 mm x 0.6 mm Right Angle SMD Chip LED Lamp



DESCRIPTIONS

- The Hyper Red source color devices are made with AlGaInP on GaAs substrate Light Emitting Diode
- The Super Bright Yellow device is made with AlGaInP (on GaAs substrate) light emitting diode chip
- · Electrostatic discharge and power surge could damage the LEDs
- · It is recommended to use a wrist band or anti-electrostatic glove when handling the LEDs
- · All devices, equipments and machineries must be electrically grounded

FEATURES

- Side Looking Dual Color Chip LED, 0.6 mm thickness
- Low power consumption
- Wide viewing angle
- · Ideal for backlight and indicator
- EIA STD package
- · Tinned pads for improved solderability
- Package: 2000 pcs / reel
- Moisture sensitivity level: 3
- Halogen-free
- RoHS compliant

APPLICATIONS


- Backlight
- · Status indicator
- Home and smart appliances
- · Wearable and portable devices
- · Healthcare applications

ATTENTION


Observe precautions for handling electrostatic discharge sensitive devices




PACKAGE DIMENSIONS










RECOMMENDED SOLDERING PATTERN



Notes

 All dimensions are in millimeters (inches).
Package dimensions tolerance is ±0.1(0.004") unless otherwise noted.
The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.

The device has a single mounting surface. The device must be mounted according to the specifications. For right angle SMD LEDs, the solder stencil should be at least 5mil in thickness, to prevent poor solder wetting due to insufficient solder paste.

SELECTION GUIDE

Part Number	Emitting Color (Material)	Lens Type	lv (mcd) @ 20mA ^[2]		Viewing Angle ^[1]	
			Min.	Тур.	201/2	
		- Water Clear	60	240		
	Hyper Red (AlGaInP)		*20	*80	440°	
KPBA-2006SURKSYKC	Super Bright Yellow (AlGaInP)		40	100	140°	
			*40	*100		

Notes

1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
Luminous intensity / luminous flux: +/-15%.
* Luminous intensity value is traceable to CIE127-2007 standards.

ELECTRICAL / OPTICAL CHARACTERISTICS at T_A=25°C

Parameter	Symbol	Emitting Color	Value		Unit
Falameter			Тур.	Max.	Unit
Wavelength at Peak Emission I_F = 20mA	λ_{peak}	Hyper Red Super Bright Yellow	645 590	-	nm
Dominant Wavelength I _F = 20mA	λ_{dom} ^[1]	Hyper Red Super Bright Yellow	630 590	-	nm
Spectral Bandwidth at 50% Φ REL MAX I _F = 20mA	Δλ	Hyper Red Super Bright Yellow	28 20	-	nm
Forward Voltage I _F = 20mA	V _F ^[2]	Hyper Red Super Bright Yellow	1.95 2.0	2.5 2.5	V
Reverse Current (V _R = 5V)	I _R	Hyper Red Super Bright Yellow	-	10 10	μA
Temperature Coefficient of λ_{peak} I_F = 20mA, -10°C \leq T \leq 85°C	TC_{\lambdapeak}	Hyper Red Super Bright Yellow	0.14 0.12	-	nm/°C
Temperature Coefficient of λ_{dom} I _F = 20mA, -10°C \leq T \leq 85°C	$TC_{\lambda dom}$	Hyper Red Super Bright Yellow	0.05 0.07	-	nm/°C
Temperature Coefficient of V _F I _F = 20mA, -10°C \leq T \leq 85°C	TCv	Hyper Red Super Bright Yellow	-1.9 -1.9	-	mV/°C

Notes:

1. The dominant wavelength (λd) above is the setup value of the sorting machine. (Tolerance λd : ±1nm.)
2. Forward voltage: ±0.1V.
3. Wavelength value is traceable to CIE127-2007 standards.
4. Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.

Parameter	Complexed	Value			
Parameter	Symbol	Hyper Red	Super Bright Yellow	Unit	
Power Dissipation	PD	75	75	mW	
Reverse Voltage	V _R	5	5	V	
Junction Temperature	TJ	115	115 115		
Operating Temperature	T _{op}	-40 To +85			
Storage Temperature	T _{stg}	-40 To +85			
DC Forward Current	I _F	30 30		mA	
Peak Forward Current	۱ _{۶Р} ^[1]	185 175		mA	
Electrostatic Discharge Threshold (HBM)	-	3000 3000		V	
Thermal Resistance (Junction / Ambient)	R _{th JA} ^[2]	730	840	°C/W	
Thermal Resistance (Junction / Solder point)	R _{th JS} ^[2]	620	710	°C/W	


ADSOLUTE MAVIMUM DATINGS SHT -35%

Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width. 2. R_{th JA}, R_{th JS} Results from mounting on PC board FR4 (pad size ≥ 16 mm² per pad). 3. Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity – Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

Kingbright


KPBA-2006SURKSYKC

TECHNICAL DATA




SPATIAL DISTRIBUTION


80 100



HYPER RED



Luminous Intensity vs. Ambient Temperature




SUPER BRIGHT YELLOW Luminous Intensity vs. Forward Current Derating Curve Luminous Intensity vs. Forward Current vs. Forward Current Ambient Temperature Forward Voltage 50 2.5 50 2.5 Luminous intensity normalised at 20 mA Luminous intensity normalised at $T_a = 25 \ ^\circ C$ Permissible forward current (mA) T_a = 25 °C T_a = 25 °C 2.0 Forward current (mA) 40 40 2.0 30 30 1.5 1.5 20 1.0 20 1.0 10 0.5 10 0.5 0 0.0 0 0.0 2.5 1.5 1.7 1.9 2.1 2.3 0 10 20 30 40 50 -40 -20 0 20 40 60 80 100 -40 -20 0 20 40 60 80 100 Forward voltage (V) Forward current (mA) Ambient temperature (°C) Ambient temperature (°C)

Kingbright

KPBA-2006SURKSYKC


REFLOW SOLDERING PROFILE for LEAD-FREE SMD PROCESS




Notes

Notes: 1. Don't cause stress to the LEDs while it is exposed to high temperature. 2. The maximum number of reflow soldering passes is 2 times. 3. Reflow soldering is recommended. Other soldering methods are not recommended as they might cause damage to the product.


TAPE SPECIFICATIONS (units : mm)



REEL DIMENSION (units : mm)



PACKING & LABEL SPECIFICATIONS



PRECAUTIONARY NOTES

(SP)XXXXXXXXXXX

- The information included in this document reflects representative usage scenarios and is intended for technical reference only. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications. 2.
- When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues. 3.
- 4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 6 All design applications should refer to Kingbright application notes available at https

RoHS Compliant