



Adjustable tilting fan head for dynamic air circulation



Slim drum design for powerful airflow



Three settings for variable fan speed



155cm power cable can be stowed when not in use



ITEM. 05613

SIP 20" HEAVY-DUTY FLOOR FAN

POWERFUL FLOOR FAN FOR EFFECTIVE AIR CIRCULATION

PRODUCT OVERVIEW

The **SIP 20" Heavy-Duty Floor Fan** uses a 5-blade design to deliver powerful airflow to help cool spaces and circulate air in a variety of indoor environments.

Fixed in a slim drum casing and mounted on a sturdy steel frame, the fan head can be tilted on its vertical axis to adjust the airflow and provide outstanding cooling and air circulation coverage.

Fans are essential in helping to provide improved air quality to indoor spaces.

FEATURES & BENEFITS

✓ POWERFUL AIRFLOW

A heavy-duty 5-blade fan is powered from a 111w motor to deliver powerful and consistent airflow coverage.

✓ VARIABLE SPEED SETTINGS

Three settings for variable fan speed:

- Low: 850rpm
- Medium: 1100rpm
- High: 1350rpm

✓ TILTING FAN HEAD

The adjustable fan head tilts on its vertical axis for dynamic circulation of air.

A robust and balanced steel frame maintains fan stability when in use.

✓ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.



**COMES WITH
A 2-YEAR
STANDARD
WARRANTY***

FIND OUT MORE AT
SIP-GROUP.COM/WARRANTY



For over 50 years, SIP Industrial Products Limited has been a flagship supplier of high-quality equipment and machinery to the ever-growing engineering, construction, automotive, and agricultural marketplaces.



ITEM. 05613

SIP 20" HEAVY-DUTY FLOOR FAN

APPLICATIONS & USES

Delivers powerful variable speed air circulation to indoor spaces.

Perfect for indoor areas such as garages, workshops and commercial buildings.

TECHNICAL INFORMATION

ITEM NO.	05613		
Input Supply	230v (13A)		
Motor Power	111w (0.14hp)		
Power Cable	155cm		
Fan Diameter	Ø 20" (508mm)		
Speed Settings	3 speed settings		
	Low	Medium	High
	850rpm	1100rpm	1350rpm
Noise Level	75dB(A)		
Net Weight	5.69kg		
Gross Weight	7.00kg		
Product Dimensions	525(H) x 605(W) x 255mm(D)		
Packaged Dimensions	555(H) x 560(W) x 180mm(D)		