



2 settings for variable fan speed



2mtr power cable, 110v input supply



Wheel-mounted steel frame for outstanding mobility



Adjustable tilting head rotates 360° on vertical axis

ITEM. 05640

SIP 30" 110v HEAVY-DUTY DRUM FAN

HEAVY-DUTY 110V DRUM FAN FOR POWERFUL INDOOR AIR CIRCULATION

PRODUCT OVERVIEW

The **SIP 30" 110v Heavy-Duty Drum Fan** delivers powerful, variable speed airflow to help cool spaces and circulate air in a variety of on-site environments.

Wheel-mounted on a cradled steel frame, the drum enclosed, heavy-duty 3-blade fan can be rotated between 360° on its vertical axis to maximise airflow coverage.

Fans are essential in helping to provide improved air quality to indoor spaces.

FEATURES & BENEFITS

✓ POWERFUL AIRFLOW

A heavy-duty 3-blade fan is powered from a 120w motor to deliver powerful and consistent airflow coverage.

✓ VARIABLE SPEED SETTINGS

Two settings for variable fan speed:

- Speed Setting 1: 850rpm
- Speed Setting 2: 950rpm

✓ DYNAMIC AIRFLOW FUNCTION

The adjustable tilting fan head can be rotated 360° on its vertical axis for greater airflow coverage.

✓ OUTSTANDING MOBILITY

The wheel-mounted, cradled steel frame is fitted with pull handles which allows the fan to be easily moved between locations for use.

✓ ENHANCED SAFETY FEATURES

Fan blades are fully enclosed with solid mesh steel guarding for greater user safety.
A robust and balanced steel frame maintains fan stability when in use.



**COMES WITH
A 2-YEAR
STANDARD
WARRANTY***

FIND OUT MORE AT
SIP-GROUP.COM/WARRANTY



For over 50 years, SIP Industrial Products Limited has been a flagship supplier of high-quality equipment and machinery to the ever-growing engineering, construction, automotive, and agricultural marketplaces.



ITEM. 05640

SIP 30" 110v HEAVY-DUTY DRUM FAN

APPLICATIONS & USES

Delivers powerful variable speed air circulation to on-site locations.

Perfect for on-site construction areas.

TECHNICAL INFORMATION

ITEM NO.	05640	
Input Supply	110v (13A)	
Motor Power	120w (0.16hp)	
Power Cable	200cm	
Fan Diameter	Ø 30" (762mm)	
Speed Settings	2 speed settings	
	Speed Setting 1	Speed Setting 2
	850rpm	950rpm
Noise Level	72dB(A)	
Net Weight	20.00kg	
Gross Weight	22.00kg	
Product Dimensions	918(H) x 918(W) x 260mm(D)	
Packaged Dimensions	735(H) x 715(W) x 230mm(D)	