

Samsung V-NAND SSD 990 PRO with Heatsink

2022 Data Sheet

Revision 1.0



LEGAL DISCLAIMER

SAMSUNG ELECTRONICS CO., LTD. RESERVES THE RIGHT TO CHANGE PRODUCTS, INFORMATION AND SPECIFICATIONS WITHOUT NOTICE.

Products and specifications discussed herein are provided for reference purposes only. All information discussed herein may change without notice and is provided on an “AS IS” basis, without warranties of any kind. This document and all information discussed herein remain the sole and exclusive property of Samsung Electronics Co., Ltd. No license of any patent, copyright, mask work, trademark or any other intellectual property right is granted under this document, by implication, estoppels or otherwise. Samsung products are not intended for use in life support, critical care, medical, safety equipment, or similar applications where product failure could result in loss of life or personal or physical harm, or any military or defense application, or any governmental procurement to which special terms or provisions may apply. For updates or additional information about Samsung products, contact your nearest Samsung representative. All brand names, trademarks and registered trademarks belong to their respective owners.

COPYRIGHT © 2022

This material is copyrighted by Samsung Electronics Co., Ltd. Any unauthorized reproductions, use or disclosure of this material, or any part thereof, is strictly prohibited and is a violation under copyright law.

TRADEMARKS & SERVICE MARKS

The Samsung logo is the trademark of Samsung Electronics Co., Ltd. All other company and product names may be trademarks of the respective companies with which they are associated.

For more information, please visit www.samsung.com/ssd and www.samsungssd.com.
To download the latest software & manuals, please visit www.samsung.com/samsungssd

TECHNICAL SPECIFICATIONS

Samsung SSD 990 PRO with Heatsink				
Usage Application	Client PCs, PlayStation®5			
Interface	PCIe Gen 4.0 x4, NVMe 2.0			
Hardware Information	Capacity ¹⁾		1TB	2TB
	Controller		Samsung in-house Controller	
	NAND Flash Memory		Samsung V-NAND TLC	
	DRAM Cache Memory		1GB LPDDR4	2GB LPDDR4
	Dimension		Max 80.0 x Max 24.3 x Max 8.2 (mm)	
	Form Factor		M.2 (2280)	
Performance (Up to.) ^{2) 3) 4)}	Sequential Read		7,450 MB/s	7,450 MB/s
	Sequential Write		6,900 MB/s	6,900 MB/s
	QD 1 Thread 1	Ran. Read	22K IOPS	22K IOPS
		Ran. Write	80K IOPS	80K IOPS
	QD 32 Thread 16	Ran. Read	1,200K IOPS	1400K IOPS
		Ran. Write	1,550K IOPS	1,550K IOPS
Power Consumption (Up to) ⁵⁾	Idle (APST on)		50mW	55mW
	Active (Avg.)	Read	5.4 W	5.8W
		Write	5.0 W	5.1W
	L1.2 mode		5 mW	
Reliability	Temp.	Operating	0°C to 70°C (Measured by S.M.A.R.T. Temperature Proper airflow recommended)	
		Non-Operating	-40°C to 85°C	
	Humidity		5% to 95% non-condensing	
	Shock	Non-Operating	1,500G(Gravity), duration: 0.5ms, 3 axis	
	Vibration	Non-Operating	20~2,000Hz, 20G	
	MTBF		1.5 million hours	
Warranty ⁶⁾	TBW		600TB	1,200TB
	Period		5 years limited	
Supporting Features	TRIM (Required OS support), Garbage Collection, S.M.A.R.T			
Data Security	AES 256-bit Full Disk Encryption, TCG/Opal V2.0, Encrypted Drive (IEEE1667)			

1) 1GB = 1,000,000,000 bytes by IDEMA. A certain portion of capacity may be used for system file and maintenance use, thus the actual available capacity may differ from the labeled capacity.

2) 990 PRO is backward compatible with PCIe 3.0.

3) Sequential and random performance measurements are based on Iometer1.1.0. Performance may vary based on SSD's firmware version, system hardware & configuration. Test System: AMD Ryzen 7 5800X 8-Core Processor CPU@3.80GHz, DDR4 3600MHz 16GBx2, OS-Windows 10 Pro 64bit, Chipset-ASRock-X570-Taichi

4) Sequential and random write performance was measured with Intelligent TurboWrite technology being activated. Intelligent TurboWrite operates only within a specific data transfer size. For detailed information, please contact your local service center

5) Power consumption is measured with Iometer1.1.0 version with AMD Ryzen 7 5800X 8-Core Processor CPU@3.80GHz, DDR4 3600MHz 16GBx2, OS-Windows 10 Pro 64bit, Chipset-ASRock-X570-Taichi

6) Samsung's warranty will be void if any of the following instructions violated.

- When assembling the 990 PRO, do not overtighten the 990 PRO with Heatsink to the motherboard.

- The 990 PRO with Heatsink has a pre-installed heat sink and it should not be removed as it can damage the device.

- The max dimensions of the 990 PRO with Heatsink with heatsink are 80.0 mm [L] x 24.3 mm [W] x 8.2mm [H]. Please check your host system provides sufficient space for installation in advance.

- Product warranty will be void if a heatsink is removed from 990 PRO with Heatsink.

7) All documented endurance test results are in compliance with JEDEC218 Standards. Please visit www.jedec.org for detailed information on JEDEC218 Standards. TBW means Terabytes Written, Warranty provides coverage for the stated time period or the TBW, whichever comes first. Please refer to the detailed warranty statement here at <http://www.samsung.com/samsungssd>

8) The LED display color may appear different from the color setting due to viewing angles and/or environmental factors

PRODUCT LINEUP

Density	Model Name	Box Contents	Model Code
1TB (1,000GB*)	MZ-V9P1T0	Samsung SSD 990 PRO with Heatsink 1TB Warranty Statement	MZ-V9P1T0CW MZ-V9P1T0GW
2TB (2,000GB*)	MZ-V9P2T0	Samsung SSD 990 PRO with Heatsink 2TB Warranty Statement	MZ-V9P2T0CW MZ-V9P2T0GW

* GB: 1GB = 1,000,000,000 bytes. The actual usable capacity may be less than the labeled capacity.

For more information, including but not limited to the warranty provided for this product, and to download the latest software & manuals, please visit www.samsung.com/ssd and www.samsungssd.com.

TEST CONFIGURATION

Below you will find a list of system configurations Samsung used to obtain the results reported in this Data Sheet. All performance data was measured with the SSD as a secondary drive

	Read/Write Performance	Power Consumption
Interface	PCIe Gen 4.0 x4	PCIe Gen 4.0 x4
OS	Windows 10 Pro 64bit	Windows 10 Pro 64bit
CPU	AMD Ryzen 7 5800X 8-Core CPU@3.80GHz	AMD Ryzen 7 5800X 8-Core CPU@3.80GHz
Memory	DDR4 3600MHz 16GBx2	DDR4 3600MHz 16GBx2
Chipset	ASRock-X570-Taichi	ASRock-X570-Taichi
Test Program	IOmeter 1.1.0	IOmeter 1.1.0

Revision History

Revision Number	Description	Revision Date
1.0	Initial Release	October, 2022