




Relays, Contactors & Switches > Switches > Switch Knobs



Switch Knob Product Type: **Knob**
Switch Knob Material: **Phenolic**
Knob Design: **Fluted**
Shaft Size: **3.17 mm [.125 in]**
Switch Knob Diameter: **19 mm [.748 in]**

Features

Product Type Features

Switch Knob Product Type	Knob
--------------------------	------

Configuration Features

Skirt	With
Spinner	Without
Spin Plate	Without
Knob Design	Fluted

Body Features

Switch Knob Material	Phenolic
Switch Knob Color	Black

Dimensions

Shaft Size	3.17 mm[.125 in]
Switch Knob Diameter	19 mm[.748 in]

Identification Marking

Indicator Style	Line
-----------------	------



Indicator Location	Top, Side & Skirt
Other	
Comment	Top spun aluminum inlay

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #5499922-2
A/L UNIV HDR 14P VERT LG LAT



TE Part #2-179552-2
DYNAMIC D-3200S TAB HSG 2P K/Y



TE Part #DT06-4S-EP11
PLG, 4P, BLK, N, SEAL RET, XCAP



TE Part #0460-256-12233
PIN, SOLID, SIZE 12,16-18AWG,PD/NI/AU



TE Part #2138530-1
STRAIN RELIEF,14 POSITION
AMPSEAL




TE Part #T4031017041-000
M8.FMLE.PNLREAR.4POS.STR



TE Part #179593-1
AMP POWER D/LOCK RECCONT. L/P



TE Part #2-1658527-2
622-1441LF=FSKT IDC S 14 30AU



TE Part #5051426-4
SAFE HIGH VOLTAGE PLUG

Documents

Product Drawings
PKES60B1/8=KNOB

English

CAD Files
Customer View Model
ENG_CVM_5-1437624-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_5-1437624-1_A.3d_stp.zip
English
Customer View Model
ENG_CVM_5-1437624-1_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Environmental Compliance



Product Compliance

English

Product Compliance

English