




Connectors > Power Connectors > Circular Power > Circular Power Connectors > One-Piece Connector, Sealed, CPC Series 1



Connector Product Type: **Housing**

Operating Voltage: **600 VDC**

Connector System: **Wire-to-Wire**

Number of Positions: **4**

Sealable: **Yes**

[All One-Piece Connector, Sealed, CPC Series 1 \(33\)](#)

Features

Product Type Features

Connector Seal Type	Wire Entry Seal
Connector Product Type	Housing
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable
Connector & Housing Type	Receptacle
Circular Connector Shell Type	All Plastic

Configuration Features

Reverse Numbering	With
Number of Positions	4
Number of Power Positions	0
Number of Signal Positions	4

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Reverse Gender	Yes
Contact Type	Socket



Contact Protection	With
--------------------	------

Mechanical Attachment

Mating Alignment Type	Keyed
Mating Alignment	With
Panel Mount Feature Type	Flange with Mounting Holes
Mating Retention Type	Threaded Coupling
Screw & Hole Thread Size	5/8-24 UNEF-2A
Polarization Code	A
Connector Mounting Type	Panel Mount
Mating Retention	With
Panel Mount Feature	With

Housing Features

Body Orientation	Straight
Housing Color	Black
Housing Material	Nylon 6/6 GF
Circular Connector Shell Size	11

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Fluid Resistance	Immersion

Operation/Application

Circuit Application	Signal
Shielded	No

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant











China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 788153-2 SLD CPC PLUG ASSY,11-4,REV SEX</p>	 <p>TE Part # CAT-AM71-C83998 CPC Heat Shrink Strain Reliefs</p>	 <p>TE Part # 1-206062-7 CABLE CLAMP KIT, BULK PKG</p>	 <p>TE Part # 81665-3 ECONOSEAL, FLANGE GASKET</p>
 <p>TE Part # 208800-1 SEALING CAP ASSY,SZ 11,CPC</p>	 <p>TE Part # 206903-2 SEALING CAP ASSY,SZ 11,CPC</p>	 <p>TE Part # 208337-1 SEAL PROTECTOR PIN</p>	 <p>TE Part # 1-2407269-4 CAP, CPC, SIZE 11 RECP &amp; 13 PLUG, YELLOW</p>






TE Part # 1-2407269-2  
CAP, CPC, SIZE 11 RECP & 13 PLUG,  
BLACK




TE Part # 1-2407269-1  
CAP, CPC, SIZE 11 RECP & 13 PLUG,  
ORANGE


Also in the Series | AMP CPC




Circular Connector Adapters(7)



Circular Connector Boots & Strain Relief(6)




Circular Connector Caps & Covers(16)




Circular Connector Hardware(3)




Circular Connector Keying Plugs(2)




Circular Connector Seals(36)




Circular Power Connectors(460)




Insertion & Extraction Tools(1)



Power Contacts(6)



Sealing Sleeves(2)




Unscreened Circular Connector Backshells & Clamps(56)

Customers Also Bought



TE Part #788155-2  
One-Piece Connector, Sealed, CPC  
Series 1



TE Part #1-163082-0  
SPEC. PLATED



TE Part #1-66601-2  
III+ SKT, 18-14, TIN, LP



TE Part #130106  
TERM, RT, SOLIS, 16-14, M5





TE Part #2103181-2  
CABLE SEAL RTNR, SIZE B, HVA280-2PI XE



TE Part #1587826-2  
CABLE SEAL, SIZE B, HVA280-2PI



TE Part #745230-5  
20DF SOCKET CONTACT,PLATED



TE Part #91513-1  
CCII HD-20 PIN SKT 22-18 ASSY



TE Part #34126  
TERMINAL,SOLIS R 16-14 3/8

Documents

Product Drawings

SLD CPC RCPT ASSY,11-4,REV SEX

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_788154-2\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_788154-2\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_788154-2\_A.3d\_stp.zip

English

3D PDF

English

Customer View Model

ENG\_CVM\_788154-2\_O.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_788154-2\_O.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_788154-2\_O.3d\_stp.zip

English





By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**  
**AMP Circular Connectors for Commercial Signal & Power Applications**  
English

**Product Specifications**  
**Product Specification**  
English

**Agency Approvals**  
**UL Report**  
English