

Finishing Sander LXT®

DBO380Z

18V • 93 x 228 mm

Finishing Sander with Built-In Dust Extraction System.

DBO380 is LXT® powered cordless Sander for accurate finishing work. It's Brushless motor is enabling greater runtime and more power. The Sander is connectable to Makita Vacuum cleaners without adapter.



Technical specifications

Brushless Motor	✓
Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Battery protection	✓
Vibrations per minute	4.000 / 8.000 / 12.000 min ⁻¹
Orbits per Minute	0 - 12000 min ⁻¹
Sanding Pad Dimensions	93 x 185 mm
Dimensions of Clamped Abrasive Sheet	93 x 228 mm
Sanding Orbit Diameter	2,0 mm
Sound Pressure Level (L _{PA})	72 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	3,6 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²

EAN 0088381752251

Link to product - www.makita.uk.com

User benefits

- High capacity dust bag with built-in vacuum adaptor for improved dust collection
- Ergonomic rubberised grip and handle designed for better fit and added comfort
- Extreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions



Related products

Standard AC

140115-2

Dust Bag



422807-8

Battery Protector



451271-6

Punch Plate



742546-7

Abrasive Paper 93-120



Optional AC

194930-6

Pad Complete Set



422807-8

Battery Protector



P-31837

Abrasive Paper 93 x 230 mm, 40G



P-31843

Abrasive Paper 93 x 230 mm, 60G



P-31859

Abrasive Paper 93 x 230 mm, 80G



P-31865

Abrasive Paper 93 x 230 mm, 100G



Other

User manual

Parts drawing