



Finishing Sander LXT®

DBO480Z

18V • 112 x 102 mm

LXT® Battery powered Finishing Sander for demanding use.

Hook & Loop type abrasive paper can be used on this Sander. Compact and lightweight structure and conveniently located on/off switch for easy one handed operation.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Maximum Output Power	210 W
Vibrations per minute	11 000 / 14 000 min ⁻¹
Orbits per Minute	11000 - 14000 min ⁻¹
Sanding Pad Dimensions	112 x 102 mm
Dimensions of Clamped Abrasive Sheet	114 x 140 mm
Pad size (triangle)	96 x 96 mm
Sanding Orbit Diameter	1,5 mm
Sound Pressure Level (L _{pA})	75 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²

User benefits

- Hook & loop type abrasive paper can be used
- Compatible with various pads
- Large clamping lever for quick and easy paper installation

EAN 0088381760720

Link to product - www.makitauk.com



Related products

Standard AC

166078-4
Dust Bag



192352-4 (2x)
Abrasive Paper Set

416063-0
Dust Bag Nozzle

416064-8
Dust Nozzle

450066-4
Hole Punch Plate



Optional AC

135246-0
Dust Box + Paper dust bag 1 pc



191Y22-2
Triangular Base Plate for DBO480 &



191Y23-0
Rectangular Base Plate Complete



191Y24-8
Base Plate



191Y25-6
Square pad (clamp)



192352-4 (2x)
Abrasive Paper Set

450066-4
Hole Punch Plate



P-35807
Abrasive Paper 114 x 102 mm, 40G



Other

User manual

Parts drawing