


PART No.
A 43 ETC.

FIRST ANGLE PROJECTION

ALTERATIONS

ISS.	C.N. No.	ALTERATION	SIG. & DATE
6	5923	FIGURE 1 ADDED	17.3.66
7		REPLACED A. 609 TO A. 608 A. 2232	7.10.68
8	11914	FIGURE 1 DELETED	8.11.68



REAM .250" DIA.

INTERNAL THREAD .375"
DIA. 32 T.P.I. OR .375" DIA.
26 T.P.I. (SEE TABLE)

N.654. N.644

MATL.	FINISH	SPEC.
BRASS		BSS.249
DURAL		BSS.1476 HEAT
	N.P.	D.T.D. 919 A
	CAD. P.	D.T.D. 904
	R. CHR.	B.S.S. 1224
	ANOD.	D.T.D. 910 C

NO.	DIM	DIM	INT. THRD	MAT.	FIN.
A43	.710	.562	3/8x32	BRASS	N.P.
A43A	.710		3/8x26	"	"
A100	.562	.562	3/8x32	"	"
A100A	.562		3/8x26	"	"
A105	.600	.562	3/8x32	"	"
A105A	.600		3/8x26	"	"
A203	.710	.562	3/8x32	"	CAD. P.
A491	.562		3/8x32	DURAL	ANOD.
A491A	.562		3/8x26	"	"
A609	.600		3/8x32	"	"
A699	.562		3/8x32	BRASS	CAD. P.
A803	.600		3/8x32	"	"
A817	.562		3/8x32	"	R. CHR.
A828	.710		3/8x32	DURAL	ANOD.

TOLERANCES
DECIMALS: ± .005"
FRACTIONS: ± 1/64"
UNLESS OTHERWISE STATED

SCALE
2:1

DIMENSIONS IN INCHES

DRAWN	CHECKED	APPROVED	DATE
B. S.	J. S. D.		7.10.68
MATERIAL:		FINISH:	
SEE TABLES			
TITLE: - SPINDLE LOCKING DEVICE		PART No. A 43 ETC.	
USED ON VARIOUS		COLVERN LTD., ROMFORD, ESSEX.	