



Magnetic Buzzer

EMX- 7T01SP




FEATURES:

- Low Frequency
- Low Voltage
- Small and Slim Size

APPLICATIONS:

- Automatic Control Equipment
- Communication Equipment
- Electronic Instruments

DIMENSIONS: (Unit: mm)



ELECTRICAL SPECIFICATIONS:

Min. Sound Pressure Level at
1.5V_{DC} /10cm ... 80dB(A)
Rated Voltage 5V DC
Operating Voltage 1~2V DC
Max. Consumption 20mA/1.5V DC
Oscillating Frequency 2300 00Hz
Operating Temperature -20~+60℃
Storage Temperature -20~+70℃
Weight 2g

PACKING INFORMATION:

Packing: 3000 pcs per export carton

Carton Size: 54725 cm

G. Weight: 6.6 kgs N. Weight: 5.1kgs

Address: No. 12. Lane 722. Sangtian Road Jiangdong Science Garden
Ningbo, 315040 P. R. China

Fax No: (0574)87803761

Tel: (0574)87802511

