



## Magnetic Buzzer

### EMX-7T12SP




#### FEATURES:

- Low Frequency
- Low Voltage
- Small and Slim Size


#### APPLICATIONS:

- Automatic Control Equipment
- Communication Equipment
- Electronic Instruments

#### DIMENSIONS:( Unit: mm)



#### CHARACTERISTICS:



#### ELECTRICAL SPECIFICATIONS :

Min. Sound Pressure Level at	
12V /10cm	85dB
Rated Voltage	DC 12V
Operating Voltage	9~15V DC
Max. Consumption	30mA/12V DC
Oscillating Frequency	±0.2kHz
Operating Temperature	-20°C+85
Weight	1.7g

#### PACKING INFORMATION:

Packing: 3000 pcs per export carton  
 Carton Size: 25 × 27 cm

G. Weight: 6.5 kgs N. Weight: 5 kgs

Address: No. 12. Lane 722Sangtian Road Jiangdong Science  
 Garden Ningbo 315040. P. R. China

Fax No: (0574)87803761

Tel: (0574) 87805605

