



Cleaners



Non-flammable
(*directive 2008/47/EC)

Reusable jet nozzle



Precision Duster with nozzle



PRECISION DUSTER

PRECISION DUSTER FOR USE WITH SEPARATE ADAPTOR

High flow duster for use with separate jet-spray nozzle for the removal of dry contamination. Compatible with industry-standard duster attachments.

- Powerful duster for use with separate precision jet nozzle
- Non-flammable* & safer in use
- Instantly removes dry contamination
- Climate friendly, low GWP of 6
- Multi-use: swap adaptors for different applications
- Brass jet nozzle eliminates potential for static build-up when used with anti-static wrist band

PRODUCT CODES / FILL SIZES



33278 / 300ml



30776 / Reusable jet nozzle

APPLICATIONS

Suitable for instant cleaning of inaccessible areas or where the use of solvents is not desirable. Can be used safely and efficiently on:

- Production line electronics
- Computers
- Optics
- Gas burner jets
- PCB's
- Precision Instruments
- Laboratory Equipment
- Photocopiers

DIRECTIONS

- Do not shake can prior to use.
- Screw on nozzle, taking care not to over-tighten.
- The product should be held in a fairly upright position and sprayed directly onto the part to be cleaned.
- Do not invert can.
- The precision jet nozzle helps to reach remote areas and components.
- If static is to be avoided ensure an earthing circuit is established with an anti-static strap or similar.
- When can is fully discharged (empty) remove nozzle and re-use.

TECHNICAL DATA

Appearance	Gas at room temperature
Odour	Slight ethereal odour
SG @ 20°C	1.18
Pressure @ 25°C	4.9 Bar
Discharge rate @ 20°C	2.8 g/sec
Solubility	Not applicable
Flammability	<p>Non-flammable (according to directive 2008/47/EC)*</p> <p>* Although classified as nonflammable by GHS, DOT, IATA and IMDG and as measured by ASTM E-681 and ISO 10156, Solstice® Propellant (HFO-1234ze) can exhibit vapor flame limits at elevated temperatures. Solstice® Propellant has a very narrow flammable range (LFL-UFL) of 8.0 - 8.5 volume percent in air at one atmosphere under the following conditions:</p> <ul style="list-style-type: none"> • Temperature is 86°F (30°C), (and) • Relative Humidity ≥50%, (and) • High energy ignition source or open flame is present <p>Accordingly, CRC recommends that for use on energized electrical equipment the ambient temperature should be below 28°C.</p>
Flashpoint	Not applicable in sealed aerosol

MATERIALS COMPATIBILITY

OK	All materials
CAUTION	-
NOT OK	-

STORAGE & SHELF LIFE

The product may be stored at normal ambient temperatures and has a shelf life of not less than 6 years with correct storage. Aerosols should always be stored below 50°C, away from direct heat and naked flame.

HEALTH AND SAFETY

A separate Safety Data Sheet (SDS) according to EC Regulation 73/404/EEC and 648/2004/EC is available from Ambersil.com or via info.uk@crcind.com

MISREPRESENTATION ACT 1967

TRADE DESCRIPTIONS ACT 1968

The information given in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which affect the use and performance of our products and for which reason no warranty is given, express or implied. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.

Version 3.1
Created: July 2019
Updated: October 2020

CRC Industries UK Ltd.
Wylds Road, Bridgwater
Somerset, TA6 4DD
United Kingdom

t +44 (0)1278 727200
f +44 (0)1278 425644
e sales.uk@crcind.com
w www.ambersil.com

Company Registered No. 04910479

VAT No. GB 821 5195 42

