



Piezo Buzzer

EFM-250




FEATURES:

- SMT Inside
- Sealed Type for Wave Soldering
- Small Size


APPLICATIONS:

- Automatic Control Equipment
- Communication Equipment
- Electronic Instruments

DIMENSIONS: (Unit: mm)



CHARACTERISTICS:



ELECTRICAL SPECIFICATIONS :

Min. Sound Pressure Level at
 12V_{DC} / 10cm .. 5dB(A)

Rated Voltage .. 12V DC

Operating Voltage .. 6~16V DC

Max. Consumption .. 8mA/12V DC

Oscillating Frequency .. 4.0 0.5 kHz

Tone Nature .. Continuous

Operating Temperature .. -25~+85 °C

Storage Temperature .. -25~+85 °C

Case Material/Color .. PC/Black

Weight .. 1g

PACKING INFORMATION:

Packing: 6000 pcs per export carton

Carton Size: 320x250x175 mm

G. Weight: 8 kgs N. Weight: 6.5 kgs

Address: No. 12. Lane 722. Sangtian Road Jiangdong Science Garden
 Ningbo, 315040 P. R. China

Fax No: (0574)87803761

Tel: (0574)87802511

