

Summary

528

AMEOF700-HAMJZ

AC-DC Converter

AMEOF700-HAMJZ





The AMEOF700-HAMJZ series is one of Aimtec's compact size 700W AC/DC converter, which is also suitable for medical equipment. It features a universal AC input of 90-264VAC and accepts a DC input voltage of 127-370VDC, with standard high efficiency, and double or reinforced isolation.

This series of converters is designed to meet IEC/EN62368, ES/EN60601, EN60335 and GB4943 standards.

This series is suitable for industrial, security, telecommunications, smart home, and medical applications.

4000

AMEOF700-HAMJZ


1000

750

125

Features

- Universal Input: 90-264VAC/127-370VDC
- Low leakage current: 0.5mA max.
- High isolation voltage: 4000VAC
- Output short circuit, over-current, overvoltage protection.
- Low no-load power consumption of 0.5W
- Suitable for Type BF application
- Designed to meet IEC/EN62368, ES/EN60601, EN60335 and GB4943 standards.



Industrial

Telecom

54



Coming Soon!

Product Training Video (click to open)

Application Notes

F 052e R4 Rev: 06/22/A

www.Aimtec.com

Power Grid

Medical



Models & Specifications

Model	Cooling Method	Input Voltage (VAC/Hz)	Nominal Output wattage (W)	Output Voltage (∨)	Output Voltage Adjustable Range (V)	Output Current (A)	Maximum capacitive load (μF)	Efficiency @230VAC Typ. (%)
AMEOF700-12SHAMJZ	Air Cooling		399.6	12	11.4 ~ 12.6	33.3	5000	92
AIVIEUF/00-125HAIVIJZ	25 CFM	Full Voltage Range	699.6	12	11.4 12.0	58.3	5000	92
AMEOF700-15SHAMJZ	Air Cooling	Full Voltage Dange	400.5	15	14.25 ~ 15.75	26.7	5000	92
AIVIEUF700-155HAIVIJZ	25 CFM	Full Voltage Range	700.5	15	14.25 15.75	46.7	5000	92
	Air Cooling	115 VAC	400.8	24	22.8 ~ 25.2	16.7	3000	94
AMEOF700-24SHAMJZ	Air Cooling	230 VAC	451.2	24		18.8		
	25 CFM	Full Voltage Range	748.8	24		31.2		
	Air Cooling	115 VAC	399.6	27	25.65 ~ 28.35	14.8	3000	94
AMEOF700-27SHAMJZ		230 VAC	450.9	27		16.7		
	25 CFM	Full voltage range	750.6	27	27.8			
	Air Cooling	115 VAC	399.6	36		11.1	2000	94.5
AMEOF700-36SHAMJZ		230 VAC	450.0	36	34.2 ~ 37.8	12.5		
	25 CFM	Full voltage range	748.8	36		20.8		
	Air Cooling	115 VAC	398.4	48		8.3	2000	
AMEOF700-48SHAMJZ		230 VAC	451.2	48	45.6 ~ 50.4	9.4		95
	25 CFM	Full Voltage Range	748.8	48		15.6		
		115 VAC	399.6	54		7.4		
AMEOF700-54SHAMJZ	Air Cooling	230 VAC	449.8	54	51.3 ~ 56.7	8.33	1000	95
	25 CFM	Full Voltage Range	750.0	54		13.89		

Input Specifications

Parameters	Conditions		Typical	Maximum	Units
ratameters	Conc		Typical	WIGAIIIIGIII	Onits
Input current	115	SVAC		8	А
input current	230		4	А	
Louisele comment	115VAC (50	А	
Inrush current	230VAC (80	А	
Lookaga	240VAC	Contact Leakage Current		0.1	mA
Leakage	240VAC		0.5	ША	
Input Frequency		47-63		Hz	
Power Factor	115 VAC (Full Load)			0.98	
	230 VAC (Full Load)			0.95	

Output Specifications

Parameters	Conditions	Typical	Maximum	Units
	12V/15V/24V/27V, 0-100% load	±2		%
Voltage accuracy	36V/48V/54V, 0-100% load	±1		%
Line regulation	Rated Load	±0.5		%
Load regulation	0%-100% Load	±1		%
Ripple & Noise*	20 MHz band width		200	mV p-p
Hold up time	115VAC/230VAC	≥10		ms
* Ripple and Noise are measured at 3	20MHz bandwidth. Please refer to the application note fo	or specific details.		



Isolation Specification						
Parameters	Conditions	Typical	Maximum	Units		
Tested I/O voltage	60 sec, leakage < 10 mA	≥4000		VAC		
Tested Input to GND	60 sec, leakage < 10 mA	≥2000		VAC		
Tested Output to GND	60 sec, leakage < 10 mA	≥1500		VAC		
Resistance I/O	100VDC	>100		MΩ		

General Specifications

Parameters		Conditions				Typical	Maximum	Units
Protection class		Class I / Cla						
Over current protection		Hiccup, Auto recovery			≥ 105		% of lout	
	12Vout						15.6	VDC
	15Vout						19.5	VDC
	24Vout		Output Voltage turn off, Re-power on for recover				31.2	VDC
Over voltage protection	27Vout						35.1	VDC
	36Vout		Re-powe		cover		46.8	VDC
	48Vout						60	VDC
	54Vout						64	VDC
Short circuit protection			Recov	ery time <	5s after the	short circuit disap	bear	
Over temperature protection			Recove	er automat	ically when t	the temperature d	rops	
No-load power consumption	Room	temperat	ure <i>,</i> 230	VAC input		0.5		W
Operating temperature		See dera	ating grap	bh		-40 to +70		°C
Storage temperature						-40 to +85		°C
Remote Sense	When RS+ and RS	When RS+ and RS- are connected to the system, with function of remote voltage compensation, if not need left RS+ and RS- open						n, if not needed,
5V Standby	5Vsb: The Loa	5Vsb: The Load capacity is 1A without fan, the load capacity is 2A with fan 25 CFM; tolerance 2%, rippl 120mVp-p(max)					e 2%, ripple:	
PS_ON Input Signal	Power O	On PS_ON High		>2	5	v		
	Power Of	ff		PS_ON L	ow	>0	0.6	v
PG Signal*	Power O	n	The PG signal goes high with 10 ms to 500 ms delay after power setup		>10	500		
	Power Off/Pow	ver Fail	The TTL signal goes low at Fail least 1 ms before output below 90% of rated value		re output	>1		
	High Leve	el		High		>2	6	
	Low Leve	el		Low		>0	0.6	
Power Derating		25.0	12V/15V(700W)		+50 to +70	>2.0		
		25 C	FIVI	Other	s(750W)	+50 to +70	>2.0	%/°C
	Operating			12V/15	V(400W)	+45 to +70	>7.9	
	Temperature Derating	Air Co		Others	90- 175(VAC)	+45 to +70	>7.0	W/80
	Ŭ	3		(450W)	176- 264(VAC)	+45 to +70	>9.0	W/°C
					MAG		0.8	%/VAC
	Input Valtage De	ratin -	90) VAC - 115	VAC		0.8	%/ VAC
	Input Voltage De	erating		7 VDC - 115			0.8	%/VAC %/VDC
Temperature coefficient	Input Voltage De	erating				±0.03		



AMEOF700-HAMJZ


AC-DC Converter

Preliminary

Weight	Open frame	625		g		
Dimensions (L x W x H)	Open frame	5.00 x 3.00 x 1.69 inches (127 x 76.2 x 43.0 mm)				
MTBF	> 200 000 hrs (MIL-HDBK -217F, t=+25°C)					
NOTE: All specifications in this datasheet are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified.						


Safety Specifications					
Parameters					
Agency approvals	Design to meet IEC/EN62368-1, ES/EN60601-1, EN60335-1, GB4943.1				
	EMC - Conducted and radiated emission	CISPR32 / EN55032, class B			
	Harmonic Current	IEC/EN61000-3-2 Class A and Class D			
	Electrostatic Discharge Immunity	IEC 61000-4-2 Contact ±8KV, Air ±15KV, Criteria A			
Standards	RF, Electromagnetic Field Immunity	IEC 61000-4-3 10V/m, Criteria A			
Stanuarus	Electrical Fast Transient/Burst Immunity	IEC 61000-4-4 ±2KV, Criteria A			
	Surge Immunity	IEC 61000-4-5 L-L ±2KV/Line to Ground ±4KV, Criteria A			
	RF, Conducted Disturbance Immunity	IEC 61000-4-6 10Vr.m.s, Criteria A			
	Voltage dips, Short Interruptions Immunity	IEC 61000-4-11 0% , 70% Criteria B			


Derating





Efficiency Curve








Dimensions

76.2



THIRD ANGLE PROJECTION



Pin-Out		Customer Connector
Pin	Mark	Housing: JST VHR-3 or equivalent
1	AC(N)	Contact: JST SVH-21T-P1.1 or
2	AC(L)	equivalent
3	+Vo	
4	-Vo	
5	FAN+	CN5: Fan power output port Housing: TKP 2502 or
6	FAN-	Molex0511910200 or equivalent Contact: TKP 54T or Molex0508028100 or equivalent
7	ADJ Output adjustable resistor	

2 - 🗖 🗖	- 1 - 3	CN6: PS_ON signal input port(3-4) 5VDC Standby output(1-2)
Pin-Out		Customer Connector
Pin	Mark	
1	+5V	Housing: TKP DH2-4P or HRS DF11- 4DS-2C or equivalent
2	GND	Contact: TKP DHT or HRS DF11-22SC or
3	PS-ON	equivalent
4	GND	

1 - 💷 🖬 3 - 💷 🖬	-	Remote sensing signal input port(1-2) PG signal(3-4)
Pin-Out		Customer Connector
Pin	Mark	
1	RS-	Housing: TKP DH2-4P or HRS DF11- 4DS-2C or equivalent
2	RS+	Contact: TKP DHT or HRS DF11-22SC or
3	GND	equivalent
4	PG	

2. Pin3, 4 connector tightening torque: M4, 1.2N. m(max)

3. General tolerances: ±1.00[±0.039]

4. The layout of the device is for reference only, please refer to the actual product 5. It is recommended 10mm distance between the PCB and other components for safety

6. Class I system (1)(2)(4) positions shall be connected to the earth (\pm)

NOTE: 1. Datasheets are updated as needed and as such, specifications are subject to change without notice. Once printed or downloaded, datasheets are no longer controlled by Aimtec; refer to www.aimtec.com for the most current product specifications. 2. Product labels shown, including safety agency certifications on labels, may vary based on the date manufactured. 3. Mechanical drawings and specifications are for reference only. 4. All specifications are measured at an ambient temperature of 25°C, humidity<75%, nominal input voltage and at rated output load unless otherwise specified. 5. Aimtec may not have conducted destructive testing or chemical analysis on all internal components and chemicals at the time of publishing this document. CAS numbers and other limited information are considered proprietary and may not be available for release. 6. This product is not designed for use in critical life support systems, equipment used in hazardous environments, nuclear control systems or other such applications which necessitate specific safety and regulatory standards other the ones listed in this datasheet. 7. Warranty is in accordance with Aimtec's standard Terms of Sale available at www.aimtec.com.