

# TECHNICAL DATA SHEET



RoHS  
Compliant

## THERMAL SWITCHES

SKUs: SW03173- SW03183



NC Thermal Switches



NO Thermal Switches

### Specifications:

Operating Temperature	One fixed point in the range of 50°C to 205°C
Temperature Tolerance	Operating temperature $\pm 5^{\circ}\text{C}$ Reset temperature: $\pm 6^{\circ}\text{C}$
Differential (Difference between on point and off point)	Normal 10°C to 30°C
Heat Resistivity	240°C
Electrical rating	15A, 125V AC (resistive load) 10° / 15A, 250V AC (resistive load)
Contact Resistance	50mΩ or less
Dielectric Strength	1,000V AC for 1 minute or more between non-live metal parts and terminals
Insulation Resistance	100MΩ or more between the non-live metal parts and terminals
Operating Life	100k cycles (class II VDE) 10K cycles (15A 250V AC estimated)

**Important Notice:** This data sheet and its contents (the "Information") belong to **multicomp**. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but **multicomp** assumes no responsibility for its accuracy or completeness any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where **multicomp** was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict **multicomp's** liability for death or personal injury resulting from its negligence.



# TECHNICAL DATA SHEET



RoHS  
Compliant

Description	Model Number
Thermal Switch, NC 50°C	T23A050ASR2-15
Thermal Switch, NC 70°C	T23A070ASR2-15
Thermal Switch, NC 90°C	T23A090ASR2-20
Thermal Switch, NC 100°C	T23A100ASR2-15
Thermal Switch, NC 112°C	T23A112ASR2-15
Thermal Switch, NC 125°C	T23A125BSR2-15
Thermal Switch, NC 150°C	T23A150BSR2-15
Thermal Switch, NO 50°C	T23B050ASR2-15
Thermal Switch, NO 60°C	T23B060ASR2-15
Thermal Switch, NO 70°C	T23B070ASR2-15
Thermal Switch, NO 90°C	T23B090ASR2-20

**Important Notice:** This data sheet and its contents (the "Information") belong to **multicomp**. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but **multicomp** assumes no responsibility for its accuracy or completeness any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where **multicomp** was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict **multicomp's** liability for death or personal injury resulting from its negligence.

