


T ☐ R ■ Metal Plate Chip Type Low Resistance Resistors (High Power)



 $\begin{aligned} \text{Coating color} &: \text{Black } (2BW(1m\,\Omega\,,1.5m\,\Omega), \ 2BP(1m\,\Omega\,,1.5m\,\Omega), \\ &\quad 3AP(0.5m\,\sim\,1.5m\,\Omega), \ 3APS(2m\,\Omega)) \end{aligned}$

■Features

- Ultra low resistances (0.5mΩ~), suitable for large current sensing.
- Ultra low height with a thickness of 0.6mm, suitable for use of small equipment.
- Excellent high-frequency characteristics.
- Automatic mounting machines are applicable.
- Suitable for reflow soldering. (Not suitable for flow soldering)
- Products meet EU-RoHS requirements.
- \bullet AEC-Q200 Tested.


Applications

- Current sensing for CPU
- Inverter power supplies
- DC-DC converters
- Mobile device etc.

■Reference Standards

IEC 60115-1 JIS C 5201-1

Construction




Dimensions

Typo		Dimensions (mm)			
Type (Inch Size Code)	Resistance (Ω)	L	W	d	t
	0.5m			1.25±0.2	0.7±0.2
	1m, 1.5m]		1.1±0.2	
2BW (1206)	2m, 3m, 4m, 5m, 6m, 7m, 8m, 9m, 10m, 11m, 12m, 13m, 15m, 16m, 18m, 20m	3.2±0.2	1.6±0.2	0.5±0.2	0.6±0.2
	0.5m	3.2±0.2	1.6±0.2	1.25±0.2	0.7 ± 0.2
	1m, 1.5m			1.1±0.2	0.6±0.2
2BP (1206)	2m, 3m, 4m, 5m, 6m, 7m, 8m, 9m, 10m, 11m, 12m, 13m, 15m, 16m, 18m, 20m			0.5±0.2	
	0.5m	5.0±0.2	2.5±0.2	1.9±0.2	0.7 ± 0.2
	1m			1.8±0.2	0.65 ± 0.2
2HW (2010)	1.5m				0.6±0.2
	2m, 2.5m, 3m, 4m, 5m, 6m			1.5±0.2	
	7m, 8m, 9m, 10m			0.5±0.2	
	0.5m		3.18±0.25	2.725±0.25	0.6±0.25
3AP (2512)	0.68m, 0.75m, 0.82m	6.35±0.25		2.675±0.25	
	1m, 1.5m, 3m, 4m			2.20±0.25	
	2m			2.50±0.25	
	5m, 6m, 7m, 8m			1.20±0.25	
	9m, 10m			0.77±0.25	
3APS (2512)	2m, 3m	6.35±0.25	3.18±0.25	1.20±0.25	0.6 ± 0.25

■Type Designation

Example



Resistance Value (Ω)	4 digits	
0.5m~0.82m	L500~L820	
1m~9m	1L00~9L00	
10m~20m	10L0~20L0	

Contact us when you have control request for environmental hazardous material other than the substance specified by EU-RoHS.


For further information on taping, please refer to APPENDIX C on the back pages.


Ratings

Turno	Power Rating	T.C.R.	Resistance Range (Ω)	Resistance Rated Terminal Part Temp.		Operating Temp.	Taping & Q'ty/Reel (pcs)	
Туре	Fower haurig	(×10 ⁻⁶ /K)	nesistance hange (12)			Range	TD	TE
TLR2BW	1.0W	±50	2m,3m,4m,5m,6m,7m,8m,9m,10m, 11m,12m,13m,15m,16m,18m,20m		+120°C and less			
ILNZBW	1.000	±75	0.5m,1m,1.5m,2m,3m,4m,5m,6m,7m,8m,9m, 10m,11m,12m,13m,15m,16m,18m,20m		+ 120 C and less			
		±50	5m,6m,7m,8m,9m,10m		+110℃ and less			
			11m,12m,13m,15m,16m,18m,20m		+100°C and less		5000	-
TLR2BP	1.5W	±75	5m,6m,7m,8m,9m,10m		+110℃ and less			
ILNZBF	ILR2BP	⊥/5	11m,12m,13m,15m,16m,18m,20m		+100°C and less			
	3.0W	±50	2m,3m,4m	F:±1%	+110℃ and less	−65°C~ +170°C		
	3.000	±75	0.5m,1m,1.5m,2m,3m,4m		+110C and less			
TLR2HW	2.0W ±50		0.5m,1m,1.5m,2m,2.5m,3m,4m,5m,6m,7m		+120°C and less		_	4000
ILITZIIVV	2.000	±75	8m,9m,10m		+ 120 C and less]		4000
	3.0W	3.0W ±50 5m,6m,7m,8m,9m,10m		5m~8m: +110°C and less				
TLR3AP	3.000	±75	5111,0111,7111,0111,9111,10111		9m~10m : +90°C and less	_		
ILNOAF	5.0W	±50	2m,3m,4m		0.5m~1m,2m~4m: +110°C and less		_	2000
	5.000	±75	0.5m,0.68m,0.75m,0.82m,1m,1.5m,2m,3m,4m		1.5m : +90°C and less			
TLR3APS	3.0W	±50,±75	2m,3m		+110°C and less			



Derating Curve






When the terminal part temperature of the resistor exceeds the rated terminal part temperature shown above, the power shall be derated according to the derating curve


*Please refer to "Introduction of the derating curves based on the terminal part temperature" on the beginning of our catalog before use.

■One-Pulse Limiting Electric Power

Please ask us about the resistance characteristic of continuous applied pulse.

The pulse endurance values are not assured values, so be sure to check the products on actual equipment when you use them.






■Thermal Resistance

Туре	Size	Resistance (Ω)	Rth (℃/W)
	2BW 2BP	0.5m	7.2
		20m	116
TLR	2HW	0.5m	9
		10m	61.1
	ЗАР	0.5m	6
		10m	62

Rth=(Hs-ts)/Power

Regarding the temperature rise, the value of the temperature varies per conditions and board for use since the temperature is measured under our measuring conditions. Please refer to us before use.

The temperature of the resistor will increase the same $\triangle T$ from the standard terminal part temperature regardlless of the ambient temperature when the same power is applied. This is because there is hardly any heat dissipation from the resistor surface to the ambient air.



Performance

Test Items	Performance Requirements Δ R%		Test Methods	
	Limit	Typical		
Resistance	Within specified tolerance	_	25℃	
T.C.R.	Within specified T.C.R.	_	+25℃/+125℃	
Resistance to soldering heat	0.5	0.3	260°C±5°C, 10s ⁺² 0s	
Rapid change of temperature	0.5	0.3	-55°C (15min.) /+150°C (15min.) 1000 cycles	
Moisture resistance	0.5	0.1	MIL-STD-202-106 0% power, 7a and 7b not required	
Biased humidity	0.5	0.1	85°C±2°C, 85%RH, 1000h, 10% Bias	
Endurance of Rated Terminal Part Temperature	1	0.3	$ \begin{array}{l} 120^{\circ}\text{C}\pm2^{\circ}\text{C}(2BW,2HW),110^{\circ}\text{C}\pm2^{\circ}\text{C}(3AP0.5m\sim1m\Omega,2m\sim8m\Omega)} \\ 90^{\circ}\text{C}\pm2^{\circ}\text{C}(3AP1.5m\Omega,9m\sim10m\Omega),110^{\circ}\text{C}\pm2^{\circ}\text{C}(3APS2m\Omega,3m\Omega),} \\ 110^{\circ}\text{C}\pm2^{\circ}\text{C}(2BP0.5m\sim10m\Omega),100^{\circ}\text{C}\pm2^{\circ}\text{C}(2BP11m\sim20m\Omega)} \\ 1000h,1.5h0N/0.5h0FFcycle \end{array} $	
I liade to see each use a successive	1	0.6	+155℃, 1000h	
High temperature exposure	2	0.8	+170°C 1000h	

■Precautions for Use

- In case of using the low ohm resistors as shunt resistors, please lay out a pattern considering the electromagnetic induction with surrounding inductors.
- In the resistance values of TLR the resistance value after soldering may change depending on the size of pad pattern or solder amount. Make sure the effect of decline/increase of resistance value before designing.