

ZW350ST

Compact high brightness short throw laser projector





- Bright WXGA DuraCore laser projector 3600 lumens and IP6X certified
- Compact and short throw lens for easy installation 360-degree and portrait projection
- Reduced power consumption for a long life span -DuraCore laser technology delivers 30,000 hours maintenance free laser light source
- External power supply More reliability, portability and energy efficiency



The ZW350ST is one of Optoma's most compact and hassle-free WXGA DuraCore laser projectors to date. Designed for maintenancefree continuous operation, this 3600-lumen projector delivers powerful image performance with flexible installation features and extensive connectivity options in a sleek, compact form factor, up to 34% smaller than previous Optoma models.¹

An added benefit, the ZW350ST features an external power supply offering more reliability, portability and energy efficiency.

DLP™ WXGA (1280x800) 3.600 lumens 300,000:1 2,000,000:1 16:9 4:3,16:9,16:10 +/-40° 1073.4 15 ~ 140Khz 24 ~ 120Hz 75%

Laser 30,000 hours

0.521:1 0.3m - 3.4m Fixed 7.51

115%

32dB

34dB

0.76m ~ 7.62m (30" ~ 300") diagonal

Inputs 2 x HDMI 1.4a 3D support

Control 1 x RS232, 1 x RJ45

Outputs 1 x Audio 3.5mm, 1 x USB-A power 1.5A

FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac

SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p, 576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz)

NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4,43MHz

Specifications
EAN: 5055387666788, Colour: White
UPC: 796435 44 641 3, Colour: Whi
Display/image
Display technology
Resolution
Brightness
Contrast ratio
Contrast ratio - dynamic
Native aspect ratio
Aspect ratio - compatible
Keystone correction - vertical
Displayable colours (millions)
Horizontal scan rate
Vertical scan rate
Uniformity
Screen size
Lamp info
Light source type
LASER life
Optical
Throw ratio
Projection distance (m)
Zoom type
Focal length (mm)

Focal length (mm) Native offset Connectivity Connections

General Noise level (typical) Noise level (max) PC compatibility 2D compatibility

3D compatibility

3D Security IP rating OSD / display languages

24/7 operation 360° operation Operating conditions Remote control Speaker count Watts per speaker In the box

Power

Yes (DLP 3D; PC frame sequential 120Hz 3D, Blu-ray DVD 3D) 720p50 / 60 Eull 3D Security bar, Kensington Lock, Password protected interface IP6X 25 languages: Arabic, Czech, Danish, Dutch, English, Farsi, Finnish, French, German, Greek, Hungarian, Indonesian, Italian, Japanese, Norwegian, Polish, Portuguese, Romanian, Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish, Vietnamese Yes Yes 0°C ~ 40°C, Max. Humidity 80%, Max. Altitude 2,500m Card style 15W AC power cord Remote control 1x CR2025 battery Basic user manual UHDCast Pro Optional wireless models External power supply, 100V ~ 240V, 50-60Hz Power supply Power consumption (standby) <0.5W Power consumption (min) 98W 139W Power consumption (max) Weight and dimensions Dimensions (W x D x H) mm 274 x 216 x 114 Gross weight 4.2 kg Net weight 3 kg







Copyright @ 2023, Optoma and its logo is a registered trademark of Optoma Corporation. Optoma Europe Ltd is the licensee of the registered trademark. All other product names and company names used herein are for identification purposes only and may be trademarks or registered trademarks of their respective owners. Errors and omissions excepted, all specifications are subject to change without notice. All images are for representation purposes only and may be simulated. ¹ Based on the comparison of the 2023 Optoma mainstream laser projectors and its previous generation. ² Comparison of 2023 Optoma mainstream laser projectors and its equivalent lamp-based counterparts. ³ Based on the packaging of 2023 Optoma laser projectors. 26052023063157